



Product: [REVConnect CAT6+ Shielded Jack](#)

REVConnect CAT6+ Shielded Jack

Product Description

REVConnect CAT6+ Shielded Jacks are available in single packs and 24 bulk packs.

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	2400 Shielded System, TIA Category 6, ISO Class E, 1GBASE-T

Physical Characteristics (Overall)

Height:	0.94 in
Width:	1.19 in
Depth:	1.63 in
Wiring Scheme:	T568A/B
Packaging:	Individually packaged in a plastic bag.
Weight:	0.048 lbs

Connectors

Materials

Description	Material	Type
Front Connection	Copper Clad Flexible PCB, 50uin Gold plated contacts over Nickel	RJ45
Rear Connection	Copper alloy, Gold plated contacts over Nickel	REVConnect
Connector Body	Nickel plated zinc alloy diecast	

Electrical Characteristics

Dielectric Strength:	1,000V RMS @ 60 Hz for 1 minute (Signals to Ground)
Current Rating:	1.300 A
Insulation Resistance:	500 M-Ohm Minimum
Max Contact Resistance:	20 mOhm
Termination Resistance:	2.5 mOhm

Temperature Range

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

Mechanical Characteristics

Footprint/Type:	KeyConnect
Tool Compatibility:	REVConnect Termination Tool (p/n RVUTT01)
Plug /Jack Compatibility:	RJ45, RJ11
Termination Front Connection:	Mated Connection
Termination Front Connection Durability:	750 cycles
Termination Rear Connection:	Mated Connection

Termination Rear Connection Durability:	20 cycles
Cable/Connector Retention:	15 lbs.
Connector/Hardware Retention:	20 lbs
Plug/Connector Retention:	11.250 lbs

Standards

UL Rating:	UL94V-0
Data Category:	Category 6+
Telecommunications Standards:	Category 6 - TIA 568.C.2, Category 6 - ISO/IEC 11801:2002 Ed.2
IEEE Specification:	Power Over Ethernet (PoE) IEEE 802.3at type 1 and 2 (up to 30W), IEEE802.3bt/D1.7 type 3 and 4 (up to 100W), CISCO UPOE (up to 60W), Power over HDBaseTTM (up to 100W)
Other Specification:	UL 1863, IEC 60603-7, FCC part 68-F

Applicable Environmental and Other Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-07-01
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL2043 Air Handling Spaces
Safety Listing:	c(UL)us Listed

Part Number

Related Parts:	Compatible with Shielded KeyConnect Patch Panels 24p and 48p, Compatible with KeyConnect Faceplates, Adapters, Boxes
----------------	--

Variants

Item #	Color	Packaging	Wiring Scheme
RV6MJKSME-B24	Metal	Bulk Pack (24)	T568A/B
RV6MJKSME-S1	Metal	Single Pack	T568A/B

Product Notes

Notes:	Please see Installation Guide PX106435.
--------	---

History

Update and Revision:	Revision Number: 0.163 Revision Date: 07-11-2019
----------------------	--

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[RV6MJKSME-S1](#) [RV6MJKSME-B24](#)