

## Video Borescope/Wireless Inspection Camera

### 17mm camera diameter and 3.5" Color TFT LCD Wireless Monitor

With optional Wireless USB Video Receiver (BRD10) to stream live video to your PC and over your VOIP (Voice Over Internet Protocol) connection

#### Features:

- Detachable wireless color display can be viewed from a remote location up to 32ft (10m) from measurement point
- 2GB microSD memory card (included) for capturing images (JPEG) or video (AVI) for viewing on your PC
- Captured video and still images with date/time stamp can be played back on the wireless monitor or your PC
- 17mm diameter camera head with 39" (1m) flexible gooseneck cable retains configured shape
- Video and images can also be transferred to your PC via the microSD card (with included SD adaptor) or USB cable (included) and viewed using Windows<sup>®</sup> Multimedia Player
- Menus in 10 languages: English, Chinese, German, French, Spanish, Portuguese, Italian, Japanese, Dutch, and Russian
- Mini water-proof (IP67) camera head for high resolution viewing
- Two bright LED lamps with dimmer to illuminate viewed object
- Glare-free close-up field of view
- Optional BR200-EXT extension cable available for increasing viewing depth; 19mm diameter connector and 37" (0.95m) cable length; maximum 2 extension cables can be connected to the borescope



Complete with 4 AA batteries, rechargeable display battery, microSD memory card with SD adaptor, USB cable, extension tools (mirror, hook, magnet), video interconnect cable, AC adaptor (100-240V, 50/60Hz), magnetic base stand, and hard case



Detachable wireless 3.5" color TFT LCD display can be viewed from a remote location up to 32ft (10m) from the measurement point.



Ideal Applications:

- Water Restoration
- HVAC and Refrigeration
- Electrical Inspection
- Automotive
- Pest control



BRD10 - Optional Wireless USB Video Receiver allows user to stream live video to a PC and also can be remotely viewed via VOIP connection



#### Ordering Information:

**BR200** .....Flexible Video Borescope (17mm diameter/1m cable)  
**BRD10** .....Wireless USB Video Receiver  
**BR200-EXT** .....Borescope Extension Cable for BR200 (19mm diameter/0.9m cable)  
**BR-4CAM** .....4.5mm Borescope Camera Head with 1m Cable  
**BR-5CAM** .....5.8mm Borescope Camera Head with 1m Cable  
**BR-9CAM** .....Replacement 9mm Borescope Camera Head with 1m Cable  
**BR-9CAM-2M** .....Replacement 9mm Borescope Camera Head with 2m Cable  
**BR-9CAM-5M** .....Replacement 9mm Borescope Camera Head with 5m Cable  
**BR-17CAM** .....Replacement 17mm Borescope Camera Head with 1m Cable  
**BR-17CAM-2M** .....Replacement 17mm Borescope Camera Head with 2m Cable  
**BR-17CAM-5M** .....Replacement 17mm Borescope Camera Head with 5m Cable  
**UA100-BR** .....Universal AC Adaptor (100-240V 50/60Hz) for BR200 and BR250  
*(Note: Recommended up to two BR200-EXT connected to BR200 to maintain resolution)*

Specifications	
<b>Camera</b>	
Pixels	712 x 486 (NTSC)
Transmission Frequency	2.4GHz
Transmission Range	32ft (10m) unobstructed view
Viewing direction	Viewing Angle 50°
Focus distance from object	5.9" to 9.8" (15 to 25cm)
Shaft diameter	0.66" (17mm)
Working length	39" (1m)
Minimum bend radius	2.36" (60mm)
Handle Dimensions	7.3 x 5.7 x 1.6" (186 x 145 x 41mm)
Weight	18.7oz (530g)
<b>Monitor</b>	
LCD Screen Type	3.5" TFT
Pixels	320 x 240
Video Output Level	0.9 to 1.3V@75Ω
Frame Rate	10, 15, 20, 25, 30FPS
Video Resolution	960 x 240 (avi format)
Image Resolution	640x 480 (jpeg format)
Monitor Dimensions	3.9 x 2.7 x 1" (100 x 70 x 25mm)
Operating/Charge Time	1.5 hours/3 hours
Weight	4.9oz (140g)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[BR200](#)