

Passive Component LCR Meter

Measures Inductance, Capacitance, and Resistance

With secondary parameter Q (Quality), D (Dissipation), R (Resistance), θ (Phase), ESR (Equivalent Series Resistance)

Features:

- Simultaneous 20,000/2,000 count backlit display of the primary parameter (L, C or R) with the secondary parameter of Q (quality), D (dissipation) R (resistance), θ (phase), or ESR (equivalent series resistance)
- Auto Select measurement function with 1kHz default test frequency
- Five test frequencies
- Set Hi/Lo limits using absolute values or percentage limits
- Relative mode function
- Parallel or Series equivalent circuit
- Auto power off with disable
- Low battery and overrange indicators
- Built-in test fixture or use external test leads
- Open and Short calibration removes unwanted stray impedances from the measurement
- Complete with test leads and 9V battery
- Optional SMD Tweezer (LCR203), plug-in SMD Component Fixture (LCR205), and pouch case (CA900)



LCR203 SMD Tweezer

LCR205 SMD Component Fixture

Specifications	Ranges	Basic Accuracy
Inductance	20 μ H, 200 μ H, 2000.0 μ H, 20.000mH, 200.00mH 2000.0H, 20.000H, 200.00H, 2000.0H	$\pm(0.5\%rdg + 5 \text{ digits})$ (DF<0.1)
Capacitance	20pF, 200pF, 2000pF, 20.000nF, 200.00nF, 2000.0nF 20.000 μ F, 200.00 μ F, 2.0000mF, 20.00mF	$\pm(0.5\%rdg + 5 \text{ digits})$ (DF<0.1)
Resistance	20.00 Ω , 200.00 Ω , 2.0000k Ω , 20.000k Ω , 200.00k Ω , 2.0000M Ω , 20.000M Ω , 200.0M Ω	$\pm(0.5\%rdg + 5 \text{ digits})$
DF (with C)	0.000 to 999	
Q	0.000 to 999	
Phase	$\pm 90^\circ$	
Test Frequency	100Hz/120Hz/1kHz/10kHz/100kHz	
Dimensions	7.6 x 3.5 x 1.6" (193 x 88 x 41mm)	
Weight	14.8oz (420g)	

Ordering Information:

LCR200Passive Component LCR Meter

Accessories

LCR203SMD Tweezer for Model LCR200

LCR205SMD Component Fixture For Model LCR200

CA900Large soft carrying case fits meter and accessories



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[LCR200](#) [LCR203](#) [LCR205](#)