Features

Regulated Converters

- 5W power in SMD package
- 4:1 Input voltage range
- Efficiency up to 86%
- 1.6kVDC/1min isolation
- Regulated output
- -40°C to +50°C at full load
- Continuous short circuit protected

Description

The R5M is an isolated 5W DC/DC converter in a compact SMD package available with 4:1 inputs covering 12, 24 and 48V rails providing single or dual regulated, short-circuit protected outputs. There is no minimum load requirement. Isolation is 1.6 kVDC/1min, and the operating temperature is from -40°C up to +50°C without derating. Class A and Class B EMC conformity requires only a few external components. Standard packaging is tube.

Selection Guide

Part Number	Input Voltage Range ⁽¹⁾ [VDC]	nom. Output Voltage [VDC]	Output Current [mA]	Efficiency typ. ⁽²⁾ [%]	max. Capacitive Load ⁽³⁾ [μF]
R5M-xx3.3S/SMD	9-36, 18-75	3.3	1000	77	4400
R5Mxx05S/SMD	9-36, 18-75	5	1000	81	2200
R5Mxx09S/SMD	9-36, 18-75	9	555	82	1470
R5M-xx12S/SMD	9-36, 18-75	12	420	84-85	1220
R5M-xx15S/SMD	9-36, 18-75	15	333	85-86	1000
R5M-xx24S/SMD	9-36, 18-75	24	210	82	470
R5M-xx05D/SMD	9-36, 18-75	±5	±500	82	±1000
R5M-xx12D/SMD	9-36, 18-75	±12	±21 <mark>0</mark>	84	±680
R5M-xx15D/SMD	9-36, 18-75	±15	±168	85	±440

Notes:

Note1: Refer to "Input Voltage Range"

Note2: Efficiency is tested at nominal input and full load at +25°C ambient Note3: Max Cap Load is tested at nominal input and full resistive load

Model Numbering



Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Parameter	Cond	dition	Min.	Тур.	Max.
Innut Valtaga Danga	nom. V _{IN}	= 24VDC	9VDC	24VDC	36VDC
Input Voltage Range	nom. V _{IN}	= 48VDC	18VDC	48VDC	75VDC
1 10 1/1	1 0000000 00000	nom. V _{IN} = 24VDC			50VDC
Input Surge Voltage	1 second max.	nom. V _{IN} = 48VDC			100VDC



R₅M

5 Watt SMD Single & Dual Output









Series


Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

BASIC CHARACTERISTICS					
Parameter	Condition		Min.	Тур.	Max.
Ouissant Current	nom. V	/ _{IN} = 24VDC		30mA	
Quiescent Current	nom. V	/ _{IN} = 48VDC		15mA	
Start-up time	power up,	power up, CTRL ON/OFF		10ms	20ms
ONLOSE OTPL (A)	DC-DC ON		open or high impedance		
ON/OFF CTRL (4)	DC-DC OFF		2mA	3mA	4mA
Standby Current	DC-	DC-DC OFF		2.5mA	
Internal Operating Frequency					
Output Ripple and Noise	201	20MHz BW		50mVp-p	
Definited Deals Director Occurrent	with external	nom. V _{IN} = 24VDC		20mAp-p	
Reflected Back Ripple Current	components	nom. V _{IN} = 48VDC		15mAp-p	


Notes:

Note4: Refer to "ON/OFF CTRL"












Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)





REGULATIONS			
Parameter	Con	dition	Value
Output Accuracy			±1.0% max.
Line Regulation	low line to hi	gh line, full load	±0.2% max.
	0% to 100% load	single	1% max.
Load Regulation	0% to 100% load	dual	1% max.
Load Negulation	10% to 90% load	single	0.5% max.
	10% to 90% toau	dual	0.8% max.
Cross Regulation	asymmetrical 2	25% / 100% load	±5% max.
Transient Response Recovery Time	25% load	step change	±500μs typ.

PROTECTIONS					
Ту	rpe	Value			
		continuous, auto recovery			
I/P to O/P	1 minute	1.6kVDC min.			
I/P to O/P, V	_{ISO} = 500VDC	$1G\Omega$ min.			
I/P to O/P,	00kHz/0.1V	50pF typ.			
	I/P to O/P I/P to O/P, V	Type			

Notes:

Note5: This power module is not internally fused. An input line fuse must always be used Recom suggests: 24Vin=T1.25A; 48Vin=T0.63A slow blow




Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

ENVIRONMENTAL			
Parameter	Condition		Value
Operating Temperature Dange	with derating		-40°C to +105°C
Operating Temperature Range	without derating		-40°C to +50°C
Maximum Case Temperature	measured at "tc point"		+105°C
Operating Humidity	non-condensing		5% - 95 <mark>% R</mark> H max.
Thermal Shock			according to MIL-STD-810F
Vibration			according to MIL-STD-810F
MTBF	according to MIL-HDBK-217F, G.B.	+25°C	2959 x 10 ³ hours


Derating Graph

(@ Chamber and natural convection 0.1m/s)



SAFETY AND CERTIFICATIONS Certificate Type (Safety) RoHS2 RoHS-2011/65/EU + AM-2015/863 EMC Compliance Condition Electromagnetic compatibility of multimedia equipment – Emission Requirements With external filter refer to "EMC Filtering" EN55032, Class A and B

EMC Filtering Suggestions according to EN55032



Class A Component List

Model	C1	C2	C3	L1
R5M-24xxS	10μF	N/A	330pF	22µH
R5M-48xxS	2.2µF	2.2µF	330pF	68µH

Class B Component List


Model	C1	C2	C3	L1
R5M-24xxS	10μF	N/A	680pF	22µH
R5M-48xxS	4.7µF	2.2µF	680pF	68µH



Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

DIMENSION AND PHYSICAL CHARACTERISTICS				
Parameter	Туре	Value		
Matarial	baseplate/case	black plastic (UL94 V-0)		
Material	potting	silicone (UL94 V-0)		
Dimension (LxWxH)		14.2 x 9.1 x 10.2mm		
Weight		2. 7g typ.		
	-			



PACKAGING INFORMATION				
Parameter	Туре	Value		
Packaging Dimension (LxWxH)	tube	218.0 x 17.2 x 19.9mm		
Packaging Quantity		20pcs		
Storage Temperature Range	non-condensing	-55°C to +125°C		
Storage Humidity		5% to 95% RH max.		

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

RECOM:

R5M-2405D/SMD R5M-2405S/SMD R5M-2409S/SMD R5M-2412D/SMD R5M-2412S/SMD R5M-2415D/SMD R5M-4812D/SMD R5M-4812S/SMD R5M-4815D/SMD R5M-4815S/SMD R5M-4824S/SMD R5M-483.3S/SMD R5M-2424S/SMD R5M-2424S/SMD R5M-243.3S/SMD R5M-4805D/SMD R5M-4805S/SMD R5M-4809S/SMD