



Product: [500PTZ](#)

PTZ, RG-59 #20, #23-1pr, #18-2c, CM, Siamese

Product Description

PTZ (CCTV + Control + Power) Cable, Rated-CM, 1-RG59 20 AWG solid bare copper with foam polyolefin, 95% bare copper braid, 1-23 AWG solid bare copper pair with polyolefin insulation, 2-18 AWG stranded bare copper conductors with polyolefin insulation, Siamese with PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Surveillance, CCTV Camera, PTZ (Pan-Tilt-Zoom)
------------------------	--

Physical Characteristics (Overall)

Conductor						
Element	AWG	Stranding	Material	Nominal Diameter	No. of Conductors	No. of Coax
Coax(es)	20	Solid	BC - Bare Copper	0.032 in		1
Pair1	23	Solid	BC - Bare Copper	0.023 in	2	
Pair2	18	7x26	BC - Bare Copper	0.047 in	2	
Conductor Count: 5						

Insulation		
Element	Material	Nominal Diameter
Coax(es)	PE - Polyethylene (Foam)	0.145 in
Pair1	PP - Polypropylene	0.041 in
Pair2	PP - Polypropylene	
Table Notes: Gas Injected		

Color Chart	
Number	Color
Coax Core	White
Pair1	Blue & White/Blue
Pair2	Black & Red

Inner Shield				
Element	Type	Material	Coverage [%]	Nominal Diameter
Coax(es)	Braid	Bare Copper (BC)	95%	0.118 in
Pair1	No Shield	No Shield		
Pair2	No Shield			

Inner Jacket	
Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.227 in
PVC - Polyvinyl Chloride	0.118 in
PVC - Polyvinyl Chloride	0.158 in

Outer Jacket	
Material	Nominal Diameter
Banana Peel (No Overall Jacket)	0.411 in

Electrical Characteristics

Conductor DCR

Element	Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Inner Shield DCR
Coax(es)	10 Ohm/1000ft	10 Ohm/1000ft	3.5 Ohm/1000ft
Pair1	20 Ohm/1000ft	20 Ohm/1000ft	
Pair2	6.5 Ohm/1000ft	6.5 Ohm/1000ft	

Capacitance

Element	Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
Coax(es)		16.3 pF/ft
Pair1	15 pF/ft	
Pair2	21.5 pF/ft	

Impedance

Element	Nominal Characteristic Impedance
Coax(es)	75 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.3 dB/100ft
5 MHz	0.65 dB/100ft
10 MHz	0.9 dB/100ft
50 MHz	1.9 dB/100ft
100 MHz	2.6 dB/100ft
200 MHz	3.6 dB/100ft
400 MHz	5 dB/100ft
700 MHz	7 dB/100ft
900 MHz	8 dB/100ft
1000 MHz	8.5 dB/100ft

Delay

Element	Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
Coax(es)	83 ns/100m	1.22 ns/ft	83%

High Frequency

Min. RL (Return Loss) [dB]
24.5 dB

Current

Element	Max. Recommended Current [A]
Coax(es)	
Pair1	2.4 Amps per Conductor at 25°C
Pair2	5 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Installation Temperature Range:	0°C To +75°C
UL Temp Rating:	75°C
Operating Temperature Range:	-10°C To +75°C
Separation Temp Range:	0°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	60 lbs/1000ft
Max. Pull Tension:	115 lbs

Standards

NEC Articles:	Article 800
---------------	-------------

NEC/(UL) Compliance:	CMR
CPR Euroclass:	Fca
RG Type:	59
Other Specification:	Video coax: RG 59/U

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1666 Vertical Shaft
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	600PTZ

Related Part Numbers

Variants

Item #	Color	UPC
500PTZ 0001000	Black, Blue, White	612825154501

Footnote:	C - CRATE REEL PUT-UP.
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents .

Product Notes

Notes:	RG59 CCTV + 1PR23 UTP + 2C 18 AWG CMR. Individually jacketed and color coded components, cabled around and each fused to a central binding spline. Cold environment installation: When installing cables that have been stored at ambient temperatures of 32 degrees Fahrenheit (0 degrees Centigrade) or lower, Belden recommends conditioning of the cable for 12 hours at room temperature prior to individual cable leg separation.
--------	---

History

Update and Revision:	Revision Number: 0.371 Revision Date: 04-29-2024
----------------------	--

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[500PTZ 0001000](#) [500PTZ 000500](#)