



**Product:** [5122FL](#)

Fire Alarm, #14-4c BC, Shielded, FPLR

## Product Description

Fire Alarm Cable, Riser-FPLR, 4-14 AWG solid bare copper conductors with PVC insulation, overall Beldfoil® shield, PVC jacket with ripcord

## Technical Specifications

### Product Overview

Suitable Applications:	Fire Alarm, Monitor/Detection, Circuits: Audio, Control, Initiating, Notification, Noisy Environment
------------------------	--

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Conductors
14	Solid	BC - Bare Copper	4

Conductor Count:	4
------------------	---

#### Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	0.01 in

#### Color Chart

Number	Color
1	Black
2	Red
3	Brown
4	Blue

#### Outer Shield

Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	22	7x28

#### Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.244 in	0.017 in	Yes

### Construction and Dimensions

#### Cabling

Twists
3.4 twist/ft

### Electrical Characteristics

#### Conductor DCR

Max. Conductor DCR	Nominal Conductor DCR
69 Ohm/km	2.43 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
31 pF/ft	55.9 pF/ft

Current

Max. Recommended Current [A]
6.4 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temperature Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	64 lbs/1000ft
Max. Pull Tension:	212.8 lbs
Min. Bend Radius/Minor Axis:	2.5 in

Standards

NEC Articles:	Article 760
NEC/(UL) Compliance:	FPLR
Other Specification:	California State Fire Marshall

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1666 Riser
CSA Flammability:	FT4
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6122FL

Related Part Numbers

Variants

Item #	Color	UPC
5122FL 0021000	Red	612825157038

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.331 Revision Date: 05-05-2023
----------------------	--

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[5122FL 0021000](#)