



**Product:** [5140U1](#) 

Security & Sound, #14-1pr, TC, CL3-FPL-PLTC, Water-Blocked

**Product Description**

Security & Sound Cable, Rated-CL3-FPL-PLTC, 1-14 AWG stranded tinned copper pair with PVC insulation, Waterblocking tape, PVC jacket

**Technical Specifications**

**Product Overview**

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Fire Alarm (Red Jkt), Power-Limited Controls, Wet Location, Below-Grade Duct
------------------------	---

**Construction Details**

**Conductor**

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	14 AWG	19x26	TC - Tinned Copper

**Insulation**

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.022 in (0.56 mm)	0.120 in (3.05 mm)	Black & Red

Waterblocking:	Waterblock Tape
----------------	-----------------

**Outer Jacket**

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.042 in (1.1 mm)	0.356 in (9.04 mm)

Overall Cable Diameter (Nominal):	0.356 in (9.04 mm)
-----------------------------------	--------------------

**Electrical Characteristics**

**Electricals**

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond
Pair(s)	3.05 Ohm/1000ft	31 pF/ft (100 pF/m)

**Voltage**

UL Voltage Rating
300 V (CL3, FPL, PLTC-ER)

**Mechanical Characteristics**

**Temperature**

UL Temperature	Operating
105°C	-30°C to +105°C

**Bend Radius**

Stationary Min.	Installation Min.
3.6 in (91 mm)	3.6 in (91 mm)

Max. Pull Tension:	95 lbs (43 kg)
Bulk Cable Weight:	59 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, Burial
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEEE 1202, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, Article 760, Article 800
CEC / C(UL) Compliance:	CL3
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.431 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	UPC
5140U1 0101000	Black	612825157205
5140U1 0021000	Red	612825157182

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[5140U1 0021000](#) [5140U1 0101000](#) [5140U1 0041000](#)