Features

Unregulated

Converters

- 3kVDC/1s or 4kVDC/1s isolation
- Optional continuous short circuit protection
- UL94V-0 package material
- Efficiency up to 84%
- Suitable for IGBT applications

RECOM DC/DC Converter

RK & RH

1 Watt SIP7 Single and Dual Output













UL60950-1 certified CSA/CAN C22.2 No. 60950-1-07 certified IEC/EN60950-1 certified IEC/EN60601-1 certified* EN55032 compliant

*+15/-9 version excluded

Description

The RK and RH Series DC/DC-Converter complements RECOM's industrial range of converters with very high isolations of 3kVDC/1s and 4kVDC/1s. The extended operating temperature range covering -40°C to +90°C is a standard feature. The converters are IEC/EN/UL60950-1 certified, and are suitable for IGBT driver applications.


Selection Guide					
Part Number	nom. Input Voltage [VDC]	Output Voltage [VDC]	Output Current [mA]	Efficiency typ. ⁽¹⁾ [%]	Max. Capacitive Load ⁽²⁾ [μF]
RK-xx05S (3,4)	5, 12, 15, 24	5	200	70-78	1000
RK-xx09S (3,4)	5, 12, 15, 24	9	111	70-80	1000
RK-xx12S (3,4)	5,12, 15, 24	12	84	78-82	470
RK-xx15S (3,4)	5, 12, 15, 24	15	66	80-82	470
RH-xx05D (3,4)	5, 12, 15, 24	±5	±100	74-78	±470
RH-xx09D (3,4)	5, 12, 15, 24	±9	±56	76-79	±470
RH-xx12D (3,4)	5, 12, 15, 24	±12	±42	78-84	±220
RH-xx15D (3,4)	5, 12, 15, 24	±15	±33	80-84	±220
RH-xx1509D (3,4)	5, 12, 24	+15/-9	+33/-56	70-81	+220/-470µF

Notes:

Note1: Efficiency is tested at nominal input and full load at +25°C ambient

Note2: Max Cap Load is tested at nominal input and full resistive load and is defined as the capacitive load that will allow start up in under 1s without damage to the converter

Model Numbering



Notes:

Note3: standard part is without Continuous Short Circuit Protection

add suffix "/P" for Continuous Short Circuit Protection

Note4: add suffix "/H" for 4kVDC/1s Isolation

or add suffix "/HP" for Continuous Short Circuit Protection and 4kVDC/1s Isolation

Ordering Examples:

RH-123.3D/P: 12V Input Voltage, ± 3.3 V Output Voltage, Dual Output with continuous short circuit protection RK-0509S/HP: 5V Input Voltage, 9V Output Voltage, Single Output with 4kVDC/1s Isolation and continuous short circuit protection





Series


Specifications (measured @ Ta= 25°C, nom. Vin, full load unless otherwise stated)


BASIC CHARACTERISTICS					
Parameter	Condition	Min.	Тур.	Max.	
Internal Input Fuse				capacitors	
Input Voltage Range			±10%		
Minimum Load		0%			
Start-up Time				250ms	
Internal Operating Frequency		50kHz	100kHz	105kHz	
Output Ripple and Noise	20MHz BW			100mVp-p	

Efficiency vs. Load












Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load unless otherwise stated)




REGULATIONS			
Parameter		Condition	Values
Output Accuracy			±5.0% max.
Line Regulation	low	line to high line	±1.2% of 1.0% Vin typ.
Load Regulation (5)	10% to 100% load	5Vout	15.0% max.
Loud Hogaldion	1070 to 10070 load	9, 12, 15Vout and RH-xx1509D	10.0% max.
Notes	:		

Note5: Operation below 10% load will not harm the converter, but specifications may not be met



Series


Specifications (measured @ Ta= 25°C, nom. Vin, full load unless otherwise stated)





Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load unless otherwise stated)



PROTECTIONS				
Parameter		Condition		Value
Short Circuit Protection (SCP)	without suffix with suffix "/P"			1 second continuous
Isolation Voltage ⁽⁶⁾	I/P to O/P	without suffix	tested for 1 second rated for 1 minute	3kVDC 1.5kVAC
		with suffix "/H"	tested for 1 second rated for 1 minute	4kVDC 2kVAC
Isolation Capacitance	RK types RH types		20pF min. / 75pF max. 20pF min. / 65pF max.	
Isolation Resistance				15G Ω min.
Insulation Grade				basic (IEC/EN60950-1) functional (IEC/EN60601-1)

Notes:

Note6: For repeat Hi-Pot testing, reduce the time and/or the test voltage

Note7: Refer to local safety regulations if input over-current protection is also required. Recommended fuse: slow blow type

ENVIRONMENTAL				
Parameter	Condition	n		Value
Operating Temperature Range	full load @ free air convec	ction (see grap	h)	-40°C to +90°C
Operating Altitude				3000m
Operating Humidity	non-condens	non-condensing		
Pollution Degree				
MTBF	according to MIL-HDBK-217F; G.B.	RK type	+25°C +85°C	992 x 10 ³ hours 145 x 10 ³ hours
		RH type	+25°C +85°C	1012 x 10³ hours 151 x 10³ hours




Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load unless otherwise stated)

Derating Graph

(@ free air convection)



SAFETY AND CERTIFICATIONS

Certificate Type (Safety)	Report / File Number	Standard
Information Technology Equipment, General Requirements for Safety	E358085-A4-UL	UL60950-1, 2nd Edition:2007
Information recimology Equipment, deficial nequirements for Safety	E330003-A4-0E	CAN/CSA C22.2 No. 60950-1-03, 2nd Edition:2007
Information Technology Equipment, General Requirements for Safety	SPCLVD1602031	IEC60950-1:2005, 2nd Edition + A2:2013
Information recrimology Equipment, deficial nequirements for Safety	3F GEVD 1002031	EN60950-1:2006 + A2:2013
Medical electrical equipment Part 1: General requirements for basic	WD-SE-R-180676-A0 (8)	IEC60601-1:2005 + A1:2012, 3rd Edition
safety and essential performance	MD-9E-U-100010-A0	EN60601-1:2006 + A1:2013 + A12:2014
EAC	RU-AT.49.09571	TP TC 004/2011
RoHS 2		RoHS-2011/65/EU + AM-2015/863


EMC Compliance	Condition	Standard / Criterion
Electromagnetic compatibility of multimedia equipment -	with external filter	EN55032, Class B
Emission requirements	(see filter suggestion below)	EN55032, Class A

Notes:

Note8: excluded +15/-9 version

EMC Filter Suggestion according to EN55032

Single Output



Component List Class A

MODEL	C1	L1	C2	C3
RK-0505S	40.5	N/A		
RK-0515S	10µF 100V MLCC	22µH choke RLS-226	N/A	N/A
RK-2405S	100V WILCO	12µH choke RLS-126		

Component List Class B

MODEL	C1	L1	C2	C3
RK-0505S	40.5	40 11 1 1	47.5	N/A
RK-0515S	10µF 100V MLCC	12µH choke RLS-126	4.7µF 50V MLCC	2.2nF
RK-2405S	100V WILCO	<u>NLO-120</u>	JUV IVILUU	N/A

Notes:

Note9: Filter suggestions are valid for indicated part numbers only. For other part numbers, please contact RECOM tech support for advice




Series


Specifications (measured @ Ta= 25°C, nom. Vin, full load unless otherwise stated)


DIMENSION and PHYSICAL CHARACTERISTICS				
Parameter	Туре	Value		
Material	case	non-conductive black plastic, (UL94 V-0)		
Material	potting	epoxy, (UL94 V-0)		
Dimension (LxWxH)	standard	19.65 x 6.0 x 10.2mm		
	with suffix "/H"	19.65 x 7.05 x 10.2mm		
Weight	standard	2.6g typ.		
	with suffix "/H"	2.8g typ.		

Dimension Drawing (mm)

Standard Version









Pinning Information


Pin#	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
5	-Vout	-Vout
6	no pin	Com
7	+Vout	+Vout

Tolerance: $xx.x = \pm 0.5mm$ $xx.xx = \pm 0.25mm$










Bottom View 1 2 5 6 7 4 x 2.54 = 10.16 6 x 2.54 = 15.24



Pinning Information


Pin#	Single	Dual
 1	+Vin	+Vin
2	-Vin	-Vin
5	-Vout	-Vout
 6	no pin	Com
7	+Vout	+Vout

Tolerance: $xx.x = \pm 0.5$ mm $xx.xx = \pm 0.25$ mm



Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load unless otherwise stated)



PACKAGING INFORMATION		
Parameter	Туре	Value
Packaging Dimension (LxWxH)	tube	520.0 x 16.0 x 9.0mm
Packaging Quantity	tube	25pcs
Storage Temperature Range		-55°C to +125°C
Storage Humidity	non-condensing	95% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.

www.recom-power.com REV.: 5/2019 EC0-8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

RECOM:

RH-0515D RK-0505S RK-0512S RK-0515S RK-1205S RK-1212S RK-1505S RK-0505S/H RK-0505S/HP RK-0505S/P RK-0505S/P RK-0509S/H RK-0509S/HP RK-0509S/P RK-0512S/H RK-0512S/HP RK-0512S/P RK-1209S/H RK-0515S/HP RK-0515S/P RK-1205S/HP RK-1205S/HP RK-1205S/P RK-1209S/H RK-1209S/H RK-1209S/H RK-1212S/HP RK-1212S/P RK-1215S/P RK-1215S/HP RK-1215S/HP RK-1215S/HP RK-1215S/HP RK-1215S/P RK-1505S/P RK-1509S/HP RK-1509S/HP RK-1509S/P RK-1512S/P RK-1512S/P RK-1512S/P RK-1512S/P RK-1512S/P RK-1512S/P RK-1515S/HP RK-1515S/HP RK-1515S/P RK-2405S/P RK-2405S/P RK-2405S/P RK-2409S/HP RK-2409S/HP RK-2409S/P RK-2412S/P RK-2412S/P RK-2412S/P RK-2412S/P RK-2412S/P RK-2415S/HP RK-2415S/P RH-0505D/P RH-0505D/H RH-0505D/H RH-0505D/HP RH-0512D/P RH-0515D/P RH-0515D/P RH-0515D/P RH-0515D/P RH-1205D/HP RH-1215D/HP RH-1215D/HP RH-1215D/HP RH-1215D/HP RH-1215D/HP RH-1215D/HP RH-1215D/HP RH-1505D/HP RH-1505