

Features


Unregulated Converters

- Industry standard pinout
- 1kVDC/1s or 2kVDC/1s basic isolation
- UL94V-0 package material
- Optional continuous short circuit protection
- Fully encapsulated
- Efficiency up to 87%

RECOM
DC/DC Converter

ROL

**0.5 Watt
SIP4
Single Output**



UL
E358085



UL60950-1 certified
CAN/CSA-C22.2 No. 60950-1-03 certified
IEC60950-1 certified
EN60950-1 certified

Description

The ROL DC/DC converters are typically used in general purpose low power isolation and voltage matching applications, and feature a full industrial operating temperature range of -40°C to +85°C without derating.

Selection Guide


Part Number	nom. Input Voltage [VDC]	Output Voltage [VDC]	Output Current [mA]	Efficiency typ. ⁽¹⁾ [%]	max. Capacitive Load ⁽²⁾ [μF]
ROL-xx05S ^(3,4)	5, 12	5	100	78-82	470
ROL-xx12S ^(3,4)	5, 12	12	42	80-86	150
ROL-xx15S ^(3,4)	5, 12	15	33	80-87	150

Notes:

Note1: Efficiency is tested at nominal input and full load at +25°C ambient

Note2: Max Cap Load is tested at nominal input and full resistive load and is defined as the capacitive load that will allow start up in under 1 s without damage to the converter

Model Numbering



Notes:

Note3: standard part is without continuous short circuit protection
add suffix „/P“ for continuous short circuit protection

Note4: add suffix „/H“ for 2kVDC isolation
or add suffix „/HP“ for continuous short circuit protection and 2kVDC isolation

Ordering Examples:

ROL-1205S/P: 12V Input Voltage, 5V Output Voltage, Single Output with continuous short circuit protection

ROL-0505S/HP: 5V Input Voltage, 5V Output Voltage, Single Output with 2kVDC Isolation and continuous short circuit protection

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm up unless otherwise stated)

BASIC CHARACTERISTICS


Parameter	Condition	Min.	Typ.	Max.
Input Voltage Range			±10%	
Minimum Load ⁽⁵⁾		0%		
Internal Operating Frequency		20kHz	54kHz	
Output Ripple and Noise	20MHz BW			100mVp-p

Notes:


Note5: Operation below 10% load will not harm the converter, but specifications may not be met

Efficiency vs. Load

ROL-0505S



ROL-0515S




REGULATIONS


Parameter	Condition	Value
Output Accuracy		±5.0% max.
Line Regulation	low line to high line	±1.2% of 1.0% Vin typ.
Load Regulation	10% to 100% load	4.0% typ. / 10.0% max.

Deviation vs. Load

ROL-0505S



ROL-0515S



Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm up unless otherwise stated)

PROTECTIONS

Parameter	Type			Value
Short Circuit Protection (SCP)	without suffix with suffix "/P"			1 second continuous
Isolation Voltage ⁽⁶⁾	I/P to O/P	without suffix	tested for 1 second rated for 1 minute	1kVDC 500VAC/60Hz
		with suffix "/H"	tested for 1 second rated for 1 minute	2kVDC 1kVAC/60Hz
Isolation Resistance				10GΩ min.
Isolation Capacitance				20pF min. / 75pF max.
Insulation Grade				basic

Notes:

Note6: For repeat Hi-Pot testing, reduce the time and/or the test voltage


Note7: Refer to local wiring regulations if input over-current protection is also required. Recommended fuse: T0.5A slow blow type

ENVIRONMENTAL

Parameter	Condition		Value
Operating Temperature Range	full load @ free air convection (see graph)		-40°C to +85°C
Operating Altitude			2000m
Operating Humidity	non-condensing		95% RH max.
Pollution Degree			PD2
MTBF	according to MIL-HDBK-217F, G.B.	+25°C +85°C	958 x 10 ³ hours 200 x 10 ³ hours

Derating Graph

(@ free air convection)



Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm up unless otherwise stated)


SAFETY AND CERTIFICATIONS

Certificate Type (Safety)	Report / File Number	Standard
Information Technology Equipment, General Requirements for Safety	1602031	IEC60950-1:2005, 2nd Edition + A2:2013 EN60950-1:2006 + A2:2013
Information Technology Equipment, General Requirements for Safety	E358085-A4-UL	UL60950-1, 2nd Edition:2007 CAN/CSA C22.2 No. 60950-1-03, 2nd Edition:2007
EAC	RU-AT.49.09571	TP TC 004/2011
RoHs 2+		RoHS-2011/65/EU + AM-2015/863

DIMENSION AND PHYSICAL CHARACTERISTICS

Parameter	Type	Value
Material	case potting PCB	non-conductive black plastic (UL94 V-0) epoxy, (UL94 V-0) FR4, (UL94 V-0)
Dimension (LxWxH)		11.5 x 6.0 x 10.0mm
Weight		1.4g typ.

Dimension Drawing (mm)



Pinning information

Pin #	Single
1	-Vin
2	+Vin
3	-Vout
4	+Vout

Tolerance:
xx.x= ±0.5mm
xx.xx= ±0.25mm

PACKAGING INFORMATION

Parameter	Type	Value
Packaging Dimension (LxWxH)	tube	520.0 x 16.0 x 9.0mm
Packaging Quantity	tube	42pcs
Storage Temperature Range		-55°C to + 125°C
Storage Humidity		95% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

RECOM:

[ROL-0505S](#) [ROL-0505S/H](#) [ROL-0505S/HP](#) [ROL-0505S/P](#) [ROL-0512S](#) [ROL-0512S/H](#) [ROL-0512S/HP](#) [ROL-0512S/P](#) [ROL-0515S](#) [ROL-0515S/H](#) [ROL-0515S/HP](#) [ROL-0515S/P](#) [ROL-1205S](#) [ROL-1205S/H](#) [ROL-1205S/HP](#) [ROL-1205S/P](#) [ROL-1212S](#) [ROL-1212S/H](#) [ROL-1212S/HP](#) [ROL-1212S/P](#) [ROL-1215S](#) [ROL-1215S/H](#) [ROL-1215S/HP](#) [ROL-1215S/P](#)