



Product: [5304FE](#)

Security & Sound, #18-6c, BC, Shielded, CMR

Product Description

Security & Sound Cable, Riser-CMR, 6-18 AWG stranded bare copper conductors with polypropylene insulation, Beldfoil® shield and PVC jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Noisy Environment
------------------------	--

Construction Details

Conductor

Element	Number of Element	AWG	Stranding	Material
Conductor(s)	6	18	7x26	BC - Bare Copper

Insulation

Element	Material	Thickness [in.]	Color Code
Conductor(s)	PP - Polypropylene	0.009	Black, Red, White, Green, Brown, Blue

Outer Shield Material

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Outer Jacket Material

Material	Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.017 in	0.224 in	Yes

Cable Diameter (Nominal):	0.224 in
---------------------------	----------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	6.5 Ohm/1000ft	27 pF/ft	48.5 pF/ft	3.5 Amps per conductor @ 25°C

Nom Outer Shield DCR:	15.25 Ohm/1000ft
-----------------------	------------------

Voltage

UL Voltage Rating
300 V (CMR)

Mechanical Characteristics

Temperature

UL Rating	Operating
75°C	-20°C to +75°C

Bend Radius

Stationary Min.	Installation Min.

2.25 in	2.2 in
---------	--------

Max. Pull Tension:	148 lbs
Bulk Cable Weight:	43 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Fire Resistance:	UL1666 Riser, IEC 60332-1-2
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMG
CPR Euroclass:	Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	6304FE

History

Update and Revision:	Revision Number: 0.252 Revision Date: 08-25-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[5304FE 008U500](#) [5304FE 0081000](#) [5304FE 008500](#)