


1. DIMENSIONS AND PARTS LIST

<DIMENSIONS>

8- $\phi 4.3 \pm 0.3$

LABEL (NOTE 1-1)





AIRFLOW DIRECTION

+50
300 0

(10)



ROTATING DIRECTION

25 ± 0.5
3 ± 0.3 3 ± 0.3



NOTE

1-1. THE PRODUCT NAME, MODEL NO., MANUFACTURER, MANUFACTURE DATE, ETC. ARE PRINTED ON LABEL.
銘板上に品名, 型名, 製造会社名 及び 製造年月日等を表示する。

<LABEL>  SHOWS LOT No.  はロットNo.を示す。


<LEAD WIRE CONNECTION TABLE>

FAN		
	LEAD WIRE	COLOR
+	UL1007 AWG24	RED
GND	UL1007 AWG24	BLACK



OR




	ECN No. E0220302	名称 Title San Ace 60 (9RA) R I B L E S S	
	単位 Unit mm	承認 Approved By TE.YAMAZAKI 24-01-10	
尺度 Scale -	図面番号 Dwg. No.	9RA0612J40021	
SANYO DENKI		承認 Approved By TE.YAMAZAKI 24-01-10	設計 Designed By P.MENDOZA 23-11-29
SANYO DENKI CO.,LTD. ISSUED		審査 Checked By R.MOLINO 24-01-10	設計 Designed By P.MENDOZA 23-11-29
Group		D12	User E0
Page		1/2	

2. GENERAL SPECIFICATIONS

<CHARACTERISTICS>

ITEM	UNIT	CHARACTERISTICS
RATED VOLTAGE	V DC	12
OPERATING VOLTAGE RANGE	V DC	7~ 13.8
MAX. AIRFLOW	m ³ /min (CFM)	1.1 (38.8)
MAX. STATIC PRESSURE	Pa (inchH ₂ O)	130 (0.52)
RATED CURRENT	A	0.35
RATED SPEED	min ⁻¹	7700±770
INSULATION RESISTANCE (NOTE 2-2)	-	10M Ω MIN. AT 500 V DC
DIELECTRIC STRENGTH (NOTE 2-2)	-	1 MINUTE AT 500 V AC, 50/60 Hz
OPERATING TEMPERATURE	℃	-20 ~ +70
STORAGE TEMPERATURE	℃	-30 ~ +70
EXPECTED LIFE	-	60,000 h / 60 ℃ (L10, CONTINUOUS OPERATION)
SOUND PRESSURE LEVEL (NOTE 2-3)	dB(A)	41
MASS	g	APPROX. 70
MATERIAL	-	FRAME, IMPELLER : PLASTICS
BEARING SYSTEM	-	2 BALL BEARINGS

<REFERENCE AIRFLOW-STATIC PRESSURE CHARACTERISTICS>



- 2-4. WITHIN THE OPERATING VOLTAGE RANGE, THE MOTOR IS PROTECTED FROM BURNOUT DUE TO LOCKED ROTOR. DO NOT LOCK ROTOR OUTSIDE OF OPERATING VOLTAGE.
使用電圧範囲にてファン拘束時焼損の恐れはない。
使用電圧範囲外でファンを拘束しないこと。
- 2-5. FAN MIGHT NOT START UP NORMALLY IF THE IMPELLER IS ROTATING WHEN THE POWER IS TURNED ON.
電源投入時、羽根が空転していると正常に起動できない場合がある。

- NOTE 2-1. ALL THE VALUES IN THE TABLE ARE TYPICAL VALUES MEASURED AFTER 30 MINUTES OF OPERATION AT ROOM TEMPERATURE AND NORMAL HUMIDITY.
表中の値はいずれも、常温、常湿、30分間動作後の標準値。
- 2-2. MEASURED BETWEEN LEAD WIRE CONDUCTORS AND FRAME.
リード線導体部とフレームとの間。
- 2-3. AT 1 m AWAY FROM THE AIR INLET.
ファン吸込側1 mにおける値。

		ECN No. E0220302	名称 Title San Ace 60 (9RA) R I B L E S S			
単位 Unit mm		新規 New Design J.VILLAR 21-09-20				
尺度 Scale -		図面番号 Dwg. No.			Rev. 9RA0612J40021 B	
SANYO DENKI			SANYO DENKI CO.,LTD. ISSUED	承認 Approved By TE.YAMAZAKI 24-01-10	審査 Checked By R.MOLINO 24-01-10	設計 Designed By P.MENDOZA 23-11-29
			Group D12	User E0	Page 2/2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Sanyo Denki:](#)

[9RA0612J40021](#)