



**Product:** [533945](#)

Surveillance CCTV, RG-6 #18 Sol BC, FPE Core, BC Braid, PVC Jkt, CMG

### Product Description

Surveillance, CCTV, RG-6, 18 AWG solid bare copper, foam PE core, 92% bare copper braid, PVC jacket, CMG

### Technical Specifications

#### Product Overview

Suitable Applications:	Surveillance, CCTV Camera
------------------------	---------------------------

#### Construction Details

RG Type:	6
----------	---

#### Conductor

AWG	Stranding	Nom. Diameter	Material
18	Solid	0.040 in	BC - Bare Copper

#### Insulation

Material	Nom. Diameter
PE - Polyethylene (Foam)	0.180 in

#### Outer Shield Material

Outer Shield Type	Material	Coverage
Braid	Bare Copper (BC)	92%

#### Outer Jacket Material

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.266 in

#### Electrical Characteristics

##### Attenuation

Frequency	Nom. Attenuation [dB/100ft]
1 MHz	0.24 dB/100ft
10 MHz	0.72 dB/100ft
50 MHz	1.50 dB/100ft
100 MHz	2.00 dB/100ft
200 MHz	2.90 dB/100ft
400 MHz	4.20 dB/100ft
700 MHz	5.60 dB/100ft
900 MHz	6.40 dB/100ft
1000 MHz	7.00 dB/100ft

##### Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedance	Nom. Velocity
6.4 Ohm/1000ft	2.7 Ohm/1000ft	16.3 pF/ft	75 Ohm	83%

##### Voltage

<b>UL Voltage Rating</b>
300 V (CMG)

## Mechanical Characteristics

### Temperature

UL Rating	Operating
75°C	-30°C to +75°C

### Bend Radius

<b>Installation Min.</b>
2.7 in

Bulk Cable Weight:	37 lbs/1000ft
Max. Pull Tension:	56 lbs

## Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Sunlight Resistance
Sustainability:	CA Prop 65, Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Fire Resistance:	UL1685 FT4 Loading, Limited Smoke, FT4
NEC / UL Compliance:	CMG
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	P-07-KA110035-MSHA

## History

Update and Revision:	Revision Number: 0.370 Revision Date: 10-19-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Belden Wire & Cable:

[533945 0101000](#) [533945 010U1000](#) [533945 009U1000](#) [533945 0091000](#) [533945 010500](#)