



Product: [5339W5](#)

Surveillance CATV MATV, RG-6 #18 BC, Duofoil® + 60% AL Braid, CM, Gel Fill

Product Description

Surveillance, CATV & MATV Cable, RG6, Rated-CM, 18 AWG solid bare copper, foam polyolefin core, Duofoil® + 60% aluminum braid, CoreGuard® gel filled, PVC jacket, UV Resistant

Technical Specifications

Product Overview

Suitable Applications:	CATV, MATV, Wet Location, Below-Grade Duct
------------------------	--

Physical Characteristics (Overall)

Conductor				
AWG	Stranding	Material	Nominal Diameter	No. of Coax
18	Solid	BC - Bare Copper	0.040 in	1
Conductor Count:				1

Insulation	
Material	Nominal Diameter
PE - Polyethylene (Foam)	0.180 in
Table Notes:	
Gas Injected	

Outer Shield				
Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Aluminum	Duofoil®	60%
Table Notes:				CoreGuard®

Outer Jacket	
Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.27 in

Electrical Characteristics

Conductor DCR				
Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
6.5 Ohm/1000ft	6.5 Ohm/1000ft		9 Ohm/1000ft	9.0 Ohm/1000ft

Capacitance
Nom. Capacitance Conductor to Shield
16.2 pF/ft

Inductance
Nominal Inductance
0.097 µH/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
4 MHz	0.6 dB/100ft
30 MHz	1.33 dB/100ft
211 MHz	3.08 dB/100ft
270 MHz	3.5 dB/100ft
300 MHz	3.7 dB/100ft
330 MHz	3.89 dB/100ft
400 MHz	4.3 dB/100ft
450 MHz	4.58 dB/100ft
550 MHz	5.09 dB/100ft
750 MHz	6 dB/100ft
870 MHz	6.5 dB/100ft
1000 MHz	7 dB/100ft

Delay

Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
83 ns/100m	1.24 ns/ft	82%

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-40°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	28 lbs/1000ft
Max. Pull Tension:	50 lbs
Min. Bend Radius/Minor Axis:	2.7 in

Standards

NEC/(UL) Compliance:	CL2, CM
CEC/C(UL) Compliance:	CM
CPR Euroclass:	Eca
RG Type:	6

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	Yes - When supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT1
UL Flammability:	UL1685 UL Loading

IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Put-Up Type	Length	UPC
5339W5 0101000	Black	Reel	1,000 ft	612825161004
5339W5 010U1000	Black	UnReel	1,000 ft	612825160991

Product Notes

Notes:	Print legend includes sequential footage marks.
--------	---

History

Update and Revision:	Revision Number: 0.399 Revision Date: 12-15-2021
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[5339W5 0101000](#) [5339X5 0101000](#) [5339W5 010500](#) [5339W5 010U1000](#)