

MODEL TLP-97111/A/SM

Ordering: P/N 61971111400

Termination: Flying Leads

TECHNICAL DATA


(Typical values @+25°C for batteries stored for one year or less)

Capacity to 3.0V (@0.5A @1% duty cycle)	1.65 Ah
Nominal voltage	3.6 V
Maximum 1 second pulse to 3.0V	3 A
Maximum pulse length @0.5A to 2.8V	1000 sec
Delay time to 3.0V @0.5A	No Delay
Weight	45 gr
Operating temperature range	-40°C to +85°C
Capacity retention after 10 years	80%



***TADIRAN
LITHIUM
BATTERIES***

PulsesPlus™

- **HIGH ENERGY**
- **UP TO 3A PULSE CAPABILITY**
- **INSTANT VOLTAGE RESPONSE**
- **NO PASSIVATION EFFECT**



See dimensions on the next page



For High Pulse Current Applications


Note: Any presentations in this data sheet concerning performance are for information purpose only and are not construed as warranties either expressed or implied, of future performance.

Rev. B Jul/04

MODEL TLP-97111/A/SM





The battery is designed specifically for applications requiring low background currents combined with high current pulses. The Pulses Plus™ battery combines the inherent benefits of bobbin type Lithium Thionyl Chloride cell with a novel hermetically sealed Hybrid Layer Capacitor (HLC). The addition of the HLC enhances the performance of the Lithium Thionyl Chloride cell to meet large pulse current requirements, thus providing greater performance and safety in comparison to jellyroll construction (spirally wound) type batteries.

* The PTC is optional and not necessary in many cases.



TADIRAN
LITHIUM
BATTERIES

PulsesPlus™



For High Pulse Current Applications

Note: Any presentations in this data sheet concerning performance are for information purpose only and are not construed as warranties either expressed or implied, of future performance.

Rev. C Dec/04

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tadiran Batteries:](#)

[TLP-97111/A/SM](#)