



BERGQUIST LIQUI FORM TLF 3500CGEL

June 2020

PRODUCT DESCRIPTION

Thermally Conductive, One-Part, Curable Gel Material.

Technology	Silicone
Appearance	Gray paste
Cure	Room Temperature or Heat Cure
Application	Thermal management, TIM (Thermal Interface Material)
Application Method	Dispense from cartridge
Operating Temperature Range, Continuous or others	-60 to 200°C
UL Flammability Rating	UL 94 V-0

FEATURES AND BENEFITS

- Thermal Conductivity: 3.5 W/m-K
- 1K curable application gel for enhanced processing and excellent temperature, mechanical, and chemical stability
- Optimized shear thinning rheology for enhanced 1K dispense rate
- Excellent form stability (stays in place)
- Ultra-conforming, with excellent wet-out for low stress interface applications

BERGQUIST LIQUI FORM TLF 3500CGEL is a one part, high performance, thermally conductivity curable gel designed for demanding high reliability applications. The material will cure from within the application, at room temperature. Cure can be accelerated with the addition of heat.

As cured, BERGQUIST LIQUI FORM TLF 3500CGEL provides a soft, thermally conductive, form-in place elastomer that is ideal for fragile assemblies, capable of filling unique and intricate air voids and gaps. It is designed for applications where highly reliable vertical gap stability is required. BERGQUIST LIQUI FORM TLF 3500CGEL requires no mixing. This material's unique formulation assures a balanced mix of high thermal conductivity, good dispensing efficiency and high thermal reliability.

TYPICAL APPLICATIONS

- Automotive electronics (HEV, NEV, batteries, ECU)
- Telecommunications
- Devices requiring low assembly pressure
- Computer and peripherals
- Between heat-generating semiconductors and a heat sink

TYPICAL PROPERTIES OF UNCURED MATERIAL

Density, ASTM D792, g/cc	3.2
Shelf Life @ -20°C, days	270

TYPICAL CURE SCHEDULE

Recommended Cure

- 60 minutes @ 100°C or
- 30 minutes @ 150°C

For room temperature cure, please contact your Henkel representative for curing guidelines.

The above cure profile is a guideline recommendation. These cure conditions (time and temperature) may vary based on customers' experience and specific application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties

Dispense Rate, grams/ minute ⁽¹⁾	50
Low Shear Viscosity, ASTM D2196, Pa·s: @ 1.0 s ⁻¹	560
High Shear Viscosity, ASTM D2196, Pa·s: @ 100 s ⁻¹	220
Heat Capacity, ASTM D2169, J/g·°C	0.7
Hardness, Shore 00, ASTM D2240	60

Electrical Properties

Dielectric Strength, ASTM D149, kV/mm	10
Dielectric Constant, ASTM D150 @ 1,000Hz	8.2



Volume Resistivity @ 500 Volts, ASTM D257, 2.80×10^{11} ohm-meter

Thermal Properties

Thermal Conductivity, ASTM D5470, W/(m-K) 3.5

(1) 30cc syringe, 90 psi (621 kPa), 0.100" orifice no attachment

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

CONFIGURATIONS AVAILABLE

BERGQUIST LIQUI FORM TLF 3500CGEL is available with glass beads optional. Glass beads are available in 7 mil configuration.

BERGQUIST LIQUI FORM TLF 3500CGEL is supplied in:

Cartridges	150cc, 300cc, 600cc
Pail	1 gallon, 4.3gallon

STORAGE

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: -20°C for a 270 days shelf life, in sealed containers with moisture barrier packaging.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\text{N} \times 0.225 = \text{lb/F}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{psi} \times 145 = \text{N/mm}^2$
 $\text{MPa} = \text{N/mm}^2$
 $\text{N} \cdot \text{m} \times 8.851 = \text{lb} \cdot \text{in}$
 $\text{N} \cdot \text{m} \times 0.738 = \text{lb} \cdot \text{ft}$
 $\text{N} \cdot \text{mm} \times 0.142 = \text{oz} \cdot \text{in}$
 $\text{mPa} \cdot \text{s} = \text{cP}$

Disclaimer

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following

disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bergquist Company:](#)

[2594107](#) [2679169](#) [2679359](#) [2679361](#) [2679686](#) [2682640](#) [2682647](#) [2683150](#) [2683781](#) [2683782](#)