



Product: [6400UH](#)

Security & Sound, 2 Conductor 20 AWG, TC, Plenum

Product Description

Security & Commercial Audio Cable, 2 Conductor 20 AWG stranded (7x28) tinned copper conductors with Flamarrest® insulation, Plenum, Flamarrest® jacket with ripcord.

Technical Specifications

Product Overview

Suitable Applications:	Intercom/PA Systems, Sound/Audio Systems
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	20 AWG	7x28	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.008 in (0.20 mm)	0.052 in mm	Black, Red

Outer Shield

Material
No Shield

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.134 in

Overall Cable Diameter (Nominal):	0.134 in
-----------------------------------	----------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
11.8 Ohm/1000ft	30 pF/ft (98 pF/m)	3.9 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	0°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1.34 in (34.0 mm)	1.34 in

Max. Pull Tension:	25.2 lbs (11.4 kg)
Bulk Cable Weight:	12 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor, Outdoor
Flammability / Reaction to Fire:	NFPA 262 (UL 910), FT6
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	5400UH

History

Update and Revision:	Revision Number: 0.91 Revision Date: 02-15-2024
----------------------	---

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
6400UH 8771000	Natural	Reel	1,000 ft	612825176657
6400UH 877U1000	Natural	UnReel	1,000 ft	612825420071
6400UH 877Z1000	Natural	ReelTuff Box	1,000 ft	612825176671

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[6400UH 8771000](#) [6400UH 877U1000](#)