



# BERGQUIST LIQUI BOND TLB 400SLT

Known as BERGQUIST THERMAL LIQUI-BOND 400 SLT  
December 2018

## PRODUCT DESCRIPTION

High Performance Silicone Adhesive Sealant With An Adaptable Cure Profile.

<b>Technology</b>	Silicone
Appearance (cured)	Black
Appearance - Part A	Off-white
Appearance - Part B	Black
<b>Cure</b>	Room temperature cure or Heat cure
<b>Application</b>	Thermal management, TIM (Thermal Interface Material)
Mix Ratio by weight: Part A: Part B	1 : 1
Mix Ratio by volume: Part A: Part B	1 : 1
Operating Temperature Range	-60 to 180°C

## FEATURES AND BENEFITS

- Fast and adaptable cure
- Cures and bonds at room temperature
- Cure rate is greatly accelerated at elevated temperatures
- Room temperature storage
- Excellent elongation to break
- Thixotropic, designed for automated dispensing as FIPG (Form-In-Place Gasket)

BERGQUIST LIQUI BOND TLB 400SLT is a high performance two-part silicone sealant designed for automotive applications. BERGQUIST LIQUI BOND TLB 400SLT offers an adaptable and reliable cure at multiple temperatures, independent of ambient moisture.

BERGQUIST LIQUI BOND TLB 400SLT is targeting the automotive module market which demands a reliable silicone sealant and adhesive. This two-part silicone material cures and bonds at temperatures from 25°C up to 180°C. At elevated temperatures, the cure rate is very fast, for example at 85°C, BERGQUIST LIQUI BOND TLB 400SLT cures in 15 minutes. The cure chemistry is compatible with Henkel's BERGQUIST brand of two-part Gap Fillers.

The cure can be adapted to suit current production capabilities, providing the option to use existing product equipment and eliminate additional capital expense. A lower temperature can also be selected to save energy or a higher temperature to save time.

## TYPICAL APPLICATIONS

- Engine control modules
- Modules with large thermal mass
- Modules with temperature sensitive components
- Integrated Brake Control modules
- HEV, EV modules
- Any electronic enclosures

## TYPICAL PROPERTIES OF UNCURED MATERIAL

Mixed Viscosity, Brookfield, ASTM D2196, mPa·s (cP):: @ 1 s <sup>-1</sup>	800,000
Density, ASTM D792, g/cc	1.5
Working Time @ 25°C, minutes <sup>(1)</sup>	60
Shelf Life @ 25°C, months	6

<sup>(1)</sup> Dwell time between bead dispensed on substrate, to aluminum lap shear substrates mated together.

## TYPICAL CURE SCHEDULE

### Fixture Time

Self-Fixture (~50 psi):  
12 hours @ 25°C  
30 minutes @ 50°C  
5 minutes @ 85°C

### Adhesion

50% Adhesion:  
24 hours @ 25°C  
60 minutes @ 50°C  
10 minutes @ 85°C

90% Adhesion:  
72 hours @ 25°C  
4 hours @ 50°C  
15 minutes @ 85°C

100% Adhesion:  
7 days @ 25°C  
12 hours @ 50°C  
30 minutes @ 85°C  
Typically 100% cohesive adhesion failure.



**TYPICAL PROPERTIES OF CURED MATERIAL****Physical Properties**

Hardness, Shore A <sup>(2)</sup> , ASTM D2240	40
Elongation @ break, ASTM D412, %	400
Breaking Strength, ASTM D1458, KN/m	4.4
Flammability, UL 94	V-0
Tensile Strength, ASTM D412	MPa 2.1 (psi) (300)
Lap Shear Strength, ASTM D1002 <sup>(2)</sup>	MPa 2.1 (psi) (300)

**Electrical Properties**

Dielectric Strength, ASTM D149, V/mil / V/mm	250/ 10,000
Dielectric Constant, ASTM D150 @ 1,000 Hz	4.3
Volume Resistivity, ASTM D257, ohm-meter	1×10 <sup>12</sup>

<sup>(2)</sup> Cured at 85°C for 15 minutes, aluminum to aluminum, typical 100% cohesive failure.

**GENERAL INFORMATION**

For safe handling information on this product, consult the Safety Data Sheet, (SDS).

**Not for product specifications**

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

**CONFIGURATIONS AVAILABLE**

BERGQUIST LIQUI BOND TLB 400SLT is available in the following configurations:

Kits	400cc, 1,200cc, 10 gallon
------	---------------------------

**STORAGE**

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: 5 to 25°C for a 6 month shelf life. Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

**Conversions**

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$   
 $\text{kV/mm} \times 25.4 = \text{V/mil}$   
 $\text{mm} / 25.4 = \text{inches}$   
 $\text{N} \times 0.225 = \text{lb}$   
 $\text{N/mm} \times 5.71 = \text{lb/in}$   
 $\text{psi} \times 145 = \text{N/mm}^2$   
 $\text{MPa} = \text{N/mm}^2$   
 $\text{N} \cdot \text{m} \times 8.851 = \text{lb} \cdot \text{in}$   
 $\text{N} \cdot \text{m} \times 0.738 = \text{lb} \cdot \text{ft}$   
 $\text{N} \cdot \text{mm} \times 0.142 = \text{oz} \cdot \text{in}$   
 $\text{mPa} \cdot \text{s} = \text{cP}$

**Disclaimer****Note:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:**

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

**In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:**

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

**In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:**

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

**Trademark usage:** [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bergquist Company:](#)

[TLB400SLT-00-00-400cc](#) [TLB400SLT-00-00-10G](#) [TLB400SLT-00-00-1200cc](#)