



Product: [6543UE](#)

Security & Sound, #22-4pr, BC, CMP

**Product Description**

Security & Sound Cable, Plenum-CMP 4-22 AWG stranded bare copper pairs with Flamarrest® insulation, Flamarrest® jacket with ripcord

**Technical Specifications**

**Product Overview**

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls
------------------------	---------------------------------------------------------------------

**Construction Details**

**Conductor**

Element	No. of Elements	Size	Stranding	Material
Pair(s)	4	22 AWG	7x30	BC - Bare Copper

**Insulation**

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.009 in (0.23 mm)	0.047 in (1.2 mm)	Black & Red, Black & White, Black & Green, Black & Blue

**Outer Shield**

Material
No Shield

**Outer Jacket**

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.234 in	Yes

Overall Cable Diameter (Nominal):	0.234 in
-----------------------------------	----------

**Electrical Characteristics**

**Electricals**

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
17.6 Ohm/1000ft	25 pF/ft (82 pF/m)	4.2 Amps per Conductor at 30°C

**Voltage**

UL Voltage Rating
300 V

**Mechanical Characteristics**

**Temperature**

UL Temperature	Operating
75°C	0°C to +75°C

**Bend Radius**

Stationary Min.	Installation Min.
2.34 in (59.4 mm)	2.34 in

Max. Pull Tension:	72.8 lbs (33.0 kg)
Bulk Cable Weight:	31 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Flammability / Reaction to Fire:	NFPA 262 (UL 910), FT6
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	5543UE

History

Update and Revision:	Revision Number: 0.297 Revision Date: 05-31-2024
----------------------	--------------------------------------------------

Part Numbers

Variants

Item #	Color	UPC
6543UE 8771000	Natural	612825178415

© 2024 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[6543UE 8771000](#)