



Reliable

Efficient

Intelligent

Universal, Reliable and Long Lasting. The Power for Wireless, Intelligence, and the Future.

The Cita Technologies CPWLD 14 is a conservatively rated, highly reliable, all-weather LED driver specifically suited for the modern demands of commercial solid state lighting. A universal input / output design adapts to a wide range of line and string voltages, allowing for worldwide implementation from a single SKU. Fully variable Multiple Dimming Control delivers analog-like smoothness with zero flicker. The additional 12V auxiliary output provides a separate power source for wireless and/or control interfaces. Cita is proud to design and manufacture all of its own LED drivers, and stands behind them with a 5 year limited warranty.

KEY FEATURES:

- **Universal Input and Output (100VAC - 305VAC)**
- **12V auxiliary output available for secondary interface**
- **Excellent 0-10V dimming performance with no flicker**
- **Compatible with IEC 60929:2006 - 0-10V ballast controls**
- **Ultra compact design**
- **Product Assurance: 5 Year Limited Warranty**
(see warranty terms for more information)
- Smooth light output promotes longer LED life
- Fully optimized design produces clean waveforms, reducing noise and stress on components.
- Multiple Dimming control interface and wireless ready
- Fully potted design meets UL IP67
- Highly reliable in wet locations
- Excellent protection features with auto recovery for all conditions
- Long Lifetime Expectancy: >100K hours @ 50°C ambient / full load
- Low standby (Off) power: 0.2W @ 120VAC; 0.4W @ 230VAC

APPLICATIONS:

Wide Variety of LED lighting fixtures:

- Indoor and outdoor
- Dimming and non dimming
- Industrial, commercial, and residential
- Remotely power wireless controllers, including Bluetooth™
- Worldwide acceptance
- Wireless mesh network ready



UL INFORMATION:

- 14W LED Driver
CC up to 1050mA, 60VDC
CV up to 1050mA, 12V-60VDC
- EN60950-1, 2nd Edition, Class 2, IP67
- UL File: E354816

ORDERING INFORMATION:

- **CPWLD 14-18U-070:**
12-22VDC @ 700mA, Dimming, no AUX
- **CPWLD 14-18U-070A:**
15-22VDC @ 700mA, Dimming + 100mA AUX
- **CPWLD 14-36U-035:**
12-42VDC @ 350mA, Dimming, no AUX
- **CPWLD 14-36U-035B:**
15-42VDC @ 350mA, Dimming + 200mA AUX
- **CPWLD 14-xxU-yyy(A/B):**
Custom CC models
- **CPWLD 14-zz-00:**
Custom CV Models
zz = 12, 24, 36, 48, 60 or upon request

CITA Technologies, L.L.C.

975 Deerfield Pkwy, Buffalo Grove, Illinois 60089, USA

T: 1-800-503-9180 or 1-847-419-9118 F: 1-847-419-1515


citapower.com

Operating Specifications

Electrical		Environmental	
Input Voltage Range	100 - 305VAC (47-63Hz)	Operating Temperature	-30°C to +70°C
Input Power	Max 16W	Case Temperature	+90°C maximum
Isolation	3000VAC / 1 minute	Storage Temperature	-40°C to +105°C
Inrush Current	60A at 230VAC, 25°C cold start	Ingress Protection	IP67
Power Factor	60% Typical	Case Material	UL94V-0 Plastic (F1)
Output Power	Max 14W	Safety Agency Approvals	
Output Voltage Range	-035 version: 350mA +/-2%, 12-42VDC, 4-12 LED string -070 version: 700mA +/-2%, 12-22VDC, 4-5 LED string -035B version: 350mA +/-2%, 15-42VDC, 5-12 LED string -070A version: 700mA +/-2%, 15-22VDC, 5 LED string All models with turn off capability (DIM <1V)	EN60950-1, 2nd edition, Class 2, IP67, for wet location use	CB Certificate No: E354816-A1-CB-1
Auxiliary Output	-035B version: 12VDC, 200mA maximum -070A version: 12VDC, 100mA maximum (-035 and -070 versions: no auxiliary output)	UL file number: E354816, standards: UL 60950-1, 2nd Edition	Standards: IEC 60950-1(ed.2), IEC 60950 1(ed.2);am1 EN 60950-1:2006/ A11:2009/ A1:2010/ A12:2011
Efficiency	Typical, full load, 14W = 83% Typical, min. LED string, or at -30°C = 70%	CSA C22.2 No. 60950-1-07, 2nd Edition	EMI Standards: CE, EN 55022, Class B; FCC Part 15, Class B
MTBF Lifetime	>500,000 hours @ 50°C ambient, full load >100,000 hours @ 60°C ambient, full load >27,000 hours @ 70°C ambient, full load		
Dimming Control	Wireless dimming interface with 12VDC power output 0-10VDC (10% to 100% dimming) 0-10VDC dimming compatible with IEC60929:2006 controllable ballasts Potentiometer PWM dimming (1KHz/10VDC)		
Robust Protection	OVP, OCP, SCP, OTP		
Mechanical			
Main Body Size	L x W x H: 2.70" x 2.30" x 0.98" Weight: 0.30 lb See drawing below for details		

Notes:

1. This product is not intended to function with TRIAC dimmer
2. Wire Leads: Input: 18AWG, 105°C, 600V; Output: 22AWG, 105°C, 600V
3. Red (AUX+) wire only for models with auxiliary output.



L1 **CITA** CE C **UL** **US** AUX+ GND(-) CTRL+
 L2 UL 60950-1

14W UNIVERSAL LED DRIVER IP67
 100-305 VAC 50/60 Hz
CPWLD 14-xxU-yyzd
 DC OUTPUT: mm-aaVDC @ bbbmA Tc: 90°C
 CTRL= 0-10 VDC RoHS
 AUX OUTPUT: 12VDC @ 100 or 200 mA

yywwC 000000000 REV: z DC- DC+

xx: Nominal voltage: 12-56VDC
 yy: Nominal constant current (mA)
 d: Auxiliary designation
 mm: Minimum Voltage
 aa: Open circuit or maximum voltage: 15-60VDC
 bbb: Nominal constant current
 yywwC: Date code yyww, followed by letter "C" for mfg location
 z: Product revision

CITA Technologies, LLC
 975 Deerfield Pkwy, Buffalo Grove, Illinois 60089, USA
 T: 1-800-503-9180 or 1-847-419-9118 F: 1-847-419-1515
 www.citatechllc.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[BIAS Power:](#)

[CPWLD14-36U-035B](#) [CPWLD14-18U-070A](#) [CPWLD14-36U-035](#) [CPWLD14-18U-070](#)