



Product: [6663U6](#) 

Category 6 Security Cable, 4 Pair, U/UTP, CMP

Product Description

Category 6 Surveillance Cable, 4 Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Plenum-CMP, Flamarrest® PVC-LS Jacket

Technical Specifications

Product Overview

Suitable Applications:	Video, Sound & Security, Premise Horizontal Cable, Ethernet 1000BASE-T, Ethernet 100BASE-TX, Ethernet 10BASE-T, PoE++, PoE+, PoE
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents .

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
23 AWG	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
PO+FEP - Polyolefin + Fluorinated Ethylene Propylene	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Outer Jacket

Material	Material Trade Name	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	Flamarrest®	0.224 in (5.69 mm)	Yes

Overall Cable Diameter (Nominal): 0.224 in (5.69 mm)

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
93.8 Ohm/km (28.6 Ohm/1000ft)	90 pF/100m

Delay

Frequency	Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
100 MHz	537 ns/100m	45 ns/100m	72%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted) [Ohm]	Max./Min. Fitted Impedance [Ohm]	Min. TCL [dB]	Min. ELTCTL [dB]
1	2.0 dB/100m	74.3	72.3	72.3	70.3	67.8	64.8	20	100 ± 15	100 ± 15	40.0	35.0
4	3.8 dB/100m	65.3	63.3	61.5	59.5	55.8	52.7	23	100 ± 15	100 ± 15	40.0	23.0
8	5.3 dB/100m	60.8	58.8	55.4	53.4	49.7	46.7	24.5	100 ± 15	100 ± 15	40.0	16.9
10	6 dB/100m	59.3	57.3	53.3	51.3	47.8	44.8	25	100 ± 15	100 ± 15	40.0	15.0
16	7.6 dB/100m	56.2	54.3	48.7	46.7	43.7	40.7	25	100 ± 15	100 ± 15	38.0	10.9
20	8.5 dB/100m	54.8	52.8	46.3	44.3	41.8	38.8	25	100 ± 15	100 ± 15	37.0	9.0
25	9.5 dB/100m	53.3	51.3	43.8	41.8	39.8	36.8	24.3	100 ± 15	100 ± 15	36.0	7.0
31.25	10.7 dB/100m	51.9	49.9	41.2	39.2	37.9	34.9	23.6	100 ± 15	100 ± 15	35.1	5.1
62.5	15.4 dB/100m	47.4	45.4	32	30	31.9	28.9	21.5	100 ± 15	100 ± 15	32.0	

100	19.8 dB/100m	44.3	42.3	24.5	22.5	27.8	24.8	20.1	100 ± 15	100 ± 15	30.0	
155	25.2 dB/100m	41.5	39.5	16.3	14.3	23.9	20.9	18.8	100 ± 20	100 ± 15	28.1	
200	29.0 dB/100m	39.8	37.8	10.8	8.8	21.8	18.8	18	100 ± 20	100 ± 15	27.0	
250	32.8 dB/100m	38.3	36.3	5.5	3.5	19.8	16.8	17.3	100 ± 20	100 ± 15	26.0	

Voltage

UL Voltage Rating
300 V (CMP)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
75°C	-20°C To +75°C	0°C To +50°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
0.9 in (23 mm)	2.25 in (57.2 mm)

Max. Pull Tension:	40 lbs (18 kg)
Bulk Cable Weight:	25 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Plenum, Indoor
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), FT6, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
ICEA Compliance:	S-116-732
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6
Third Party Performance Verification:	Category 6
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
CENELEC Compliance:	Segregation class according EN50174-2 = a
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	5663U6

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Jacket sequentially marked at 2 ft. intervals.
--------	---

History

Update and Revision:	Revision Number: 0.559 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
6663U6 0101000	Black	612825178866	C
6663U6 010500	Black	612825178873	

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[6663U6 010500](#) [6663U6 0101000](#)