

73403WS Multi-Conductor - 600V Shielded, Light to Moderate Flexing Applications Up to 1 Million Flex Life Cycles

For more Information
please call

1-800-Belden1

General Description:

14 AWG stranded (41x30) bare copper conductors, PVC insulation, oil-resistant PVC inner jacket, tinned copper braid shield, 85% coverage, oil-resistant overall PVC jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (in.)
2	14	41x30	BC - Bare Copper	0.074

Total Number of Conductors: 3

Ground Wire

Ground Wire (Y/N):	Y
Ground Wire AWG:	14
Ground Wire Stranding:	41X30
Ground Wire Conductor Material:	BC - Bare Copper
Ground Wire Insulation Material:	PVC - Polyvinyl Chloride

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)	Dia. (in.)
PVC - Polyvinyl Chloride	0.022	0.118

Insulation Color Code Chart:

Color	Description
Black	Individually Numbered
Yellow/Green	Ground

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom Wall (in.)	Nom. Dia. (in.)
PVC - Polyvinyl Chloride	0.035	0.331

Outer Shield

Outer Shield Material:

Outer Shield Material	Coverage (%)
TC - Tinned Copper	85.000

Outer Shield Separator Material: Tissue Tape, 25% Overlap, Min.

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.042

Overall Cable

Overall Nominal Diameter: 0.443 in.

Mechanical Characteristics (Overall)

Storage Temperature Range:	-40°C To +90°C
Installation Temperature Range:	Flexing: -5°C To +90°C
Operating Temperature Range:	Flexing: -5°C To +90°C
Bulk Cable Weight:	261 lbs/1000 ft.
Max. Recommended Pulling Tension:	106 lbs.
Min. Bend Radius/Minor Axis:	2.200 in.
Min. Bend/Installation:	2.200 in.
Min. Bend Radius (Continuous Flexing):	2.200 in.
Flex Cycle Rating:	1 Million Flexes

73403WS Multi-Conductor - 600V Shielded, Light to Moderate Flexing Applications Up to 1 Million Flex Life Cycles

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	THHN/THWN Singles
AWM Specification:	UL Style 2587 (600 V 90°C)
CSA Specification:	600 V AWM I/II A/B
EU Directive 2011/65/EU (ROHS II):	Yes
Other Specification:	AWM/STYLE 2587, AWM I/II A/B, FT1, VDE 0472, Section 803 Oil Test, EU Low Voltage Directive 2014/35/EC, EU Directive 2011/65/EU(RoHS2), REACH Regulation (EC 1907/2006), California Proposition 65

Flame Test

CSA Flame Test:	FT1
-----------------	-----

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/ft)
0.170

Nom. Capacitance Cond. to Other Cond. & Ground:

Description	Freq. (kHz)	Capacitance (pF/ft)
Nom. Cond. to Cond	1.000	57.000
Nom. Ground.	1.000	103.000

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
2.600

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
2.600

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
73403WS 008100	100 FT	31.600 LB	GRAY		14AWG 41/30 3C SHIELDED
73403WS 0081000	1,000 FT	275.000 LB	GRAY		14AWG 41/30 3C SHIELDED
73403WS 008500	500 FT	139.500 LB	GRAY		14AWG 41/30 3C SHIELDED

Revision Number: 0 Revision Date: 09-27-2017

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[73403WS 008500](#) [73403WS 008100](#) [73403WS 0081000](#)