

METRIC MEASUREMENT VERSION

73407WS Multi-Conductor - 600V Shielded, Light to Moderate Flexing Applications Up to 1 Million Flex Life Cycles


 For more Information
 please call

1-800-Belden1

General Description:

14 AWG stranded (41x30) bare copper conductors, PVC insulation, oil-resistant PVC inner jacket, tinned copper braid shield, 85% coverage, oil-resistant overall PVC jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (mm)
6	14	41x30	BC - Bare Copper	1.880

Total Number of Conductors: 7

Ground Wire

Ground Wire (Y/N):	Y
Ground Wire AWG:	14
Ground Wire Stranding:	41X30
Ground Wire Conductor Material:	BC - Bare Copper
Ground Wire Insulation Material:	PVC - Polyvinyl Chloride

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)	Dia. (mm)
PVC - Polyvinyl Chloride	0.559	2.997

Insulation Color Code Chart:

Color	Description
Black	Individually Numbered
Yellow/Green	Ground

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom Wall (mm)	Nom. Dia. (mm)
PVC - Polyvinyl Chloride	0.889	10.998

Outer Shield

Outer Shield Material:

Outer Shield Material	Coverage (%)
TC - Tinned Copper	85.000

Outer Shield Separator Material: Tissue Tape, 25&#37; Overlap, Min.

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.448

Overall Cable

Overall Nominal Diameter: 14.757 mm

Mechanical Characteristics (Overall)

Storage Temperature Range:	-40°C To +90°C
Installation Temperature Range:	Flexing: -5°C To +90°C
Operating Temperature Range:	Flexing: -5°C To +90°C
Bulk Cable Weight:	729.218 Kg/Km
Max. Recommended Pulling Tension:	1067.568 N
Min. Bend Radius/Minor Axis:	73.660 mm
Min. Bend/Installation:	73.660 mm
Min. Bend Radius (Continuous Flexing):	73.660 mm
Flex Cycle Rating:	1 Million Flexes

METRIC MEASUREMENT VERSION

73407WS Multi-Conductor - 600V Shielded, Light to Moderate Flexing Applications Up to 1 Million Flex Life Cycles

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	THHN/THWN Singles
AWM Specification:	UL Style 2587 (600 V 90°C)
CSA Specification:	600 V AWM I/II A/B
EU Directive 2011/65/EU (ROHS II):	Yes
Other Specification:	AWM/STYLE 2587, AWM I/II A/B, FT1, VDE 0472, Section 803 Oil Test, EU Low Voltage Directive 2014/35/EC, EU Directive 2011/65/EU(RoHS2), REACH Regulation (EC 1907/2006), California Proposition 65

Flame Test

CSA Flame Test:	FT1
-----------------	-----

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)
0.558

Nom. Capacitance Cond. to Other Cond. & Ground:

Description	Freq. (kHz)	Capacitance (pF/m)
Nom. Cond. to Cond	1.000	187.017
Nom. Ground.	1.000	337.943

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
8.531

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
5.479

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
73407WS 008100	100 FT	54.400 LB	GRAY		14AWG 41/30 7C SHIELDED

Revision Number: 0 Revision Date: 09-27-2017

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[73407WS 008100](#)