




REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Update w/o Changes	03/10/04	M. C.
B	Image Orientation Update w/o Changes	02/23/05	M. C.
C	Updated SM1206UWC Lens Appearance	04/24/08	M. C.
D	Updated Anode Marking for SM1206HC and SM1206SRC	05/21/08	M. C.



ABSOLUTE MAXIMUM RATINGS (Ta=25° C)

REVERSE VOLTAGE	5V
REVERSE CURRENT	100uA
OPERATING TEMPERATURE RANGE	-25° C - 85° C
STORAGE TEMPERATURE	-30° C - 100° C
LEAD SOLDERING TEMPERATURE(1/16" FROM BODY)	260° C FOR 5 SECONDS

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 BIVAR [®] 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°	 TITLE: SM1206 SERIES	
.XX ± .02			
.XXX ± .010		PART NO: SM1206XXC	
DESIGNED: David Green	DATE: 04/28/04	CAGE CODE : 32559 SHEET # 1 OF 3	
CHECKED: Ty Yin	DATE: 04/28/04	CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.	
		REVISION: D	


REV.	DESCRIPTION	DATE	APPROVED
	SEE SHEET#1.		

LED Part No.	Chip			Lens Appearance	Absolute Max. Ratings				Electro-Optical Data @ 20m A			Viewing Angle 2 Θ ½ (deg)
	Material	Peak Wave Length (nm)	Emitted Color		Δλ (nm)	Pd (mW)	If (mA)	Peak If(mA)	Vf (V)		Iv (mcd)	
									TYP	MAX	TYP	
SM1206BWC	GaN/SiC	430	SUPER BLUE	WATER CLEAR	65	70	15	150	3.8	4.5	20	140
SM1206UBWC	InGaN/SiC	470	ULTRA BLUE	WATER CLEAR	30	84	20	100	3.5	4.0	90	140
SM1206PGC	GaP	555	PURE GREEN	WATER CLEAR	25	100	30	150	2.2	2.6	2	140
SM1206GC	GaP	568	GREEN	WATER CLEAR	30	100	30	150	2.2	2.6	15	140
SM1206YC	GaAsP/GaP	585	YELLOW	WATER CLEAR	35	100	30	150	2.1	2.6	15	140
SM1206UYC	AlGaInP	588	ULTRA YELLOW	WATER CLEAR	15	100	30	150	2.0	2.6	60	140
SM1206AC	GaAsP/GaP	610	AMBER	WATER CLEAR	35	100	30	150	2.0	2.6	20	140
SM1206UOC	AlGaInP	620	ULTRA ORANGE	WATER CLEAR	17	100	30	150	2.0	2.6	75	140
SM1206HC*	GaAsP/GaP	635	HE RED	WATER CLEAR	45	100	30	150	2.0	2.6	20	140
SM1206SRC*	GaAlAs/GaAs	660	SUPER RED	WATER CLEAR	20	60	30	150	1.7	2.6	30	140
SM1206URC	GaAlAs/GaAs	660	ULTRA RED	WATER CLEAR	20	80	30	150	2.0	2.6	45	140
SM1206RC	GaP	700	RED	WATER CLEAR	90	50	15	50	2.2	2.6	3	140
SM1206UWC	InGaN	X=.29 Y=.30	WHITE	YELLOW	-	84	20	100	3.5	4.0	135	140

*ANODE MARKING

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED) <u>±10% ALL VALUES</u>		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
X° ± 5° 		TITLE: SM1206 SERIES	
DESIGNED: David Green	DATE: 04/28/04	PART NO: SM1206XXC	REVISION: D
CHECKED: T. Yin	DATE: 04/28/04	CAGE CODE : 32559	SHEET # 2 OF 3
CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.			

REV.	DESCRIPTION	DATE	APPROVED
	See Sheet #1.		



2. UNLESS OTHERWISE SPECIFIED,
PACKAGING TO COMPLY WITH EIA-481-B
1. 3000 pcs PER REEL

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
<u>DECIMALS</u>	<u>ANGULAR</u>		
.X ± .1	X° ± 1°	 TITLE: SM1206 SERIES	
.XX ± .02			
.XXX ± .010		PART NO: SM1206XXC	
DESIGNED: David Green	DATE: 04/28/04	REVISION: D	
CHECKED: T. Yin	DATE: 04/28/04	CAGE CODE : 32559 SHEET # 3 OF 3 CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[BIVAR:](#)

[SM1206PGC](#)