



REV.	DESCRIPTION	DATE	APPROVED
B	Engineering Update w/o Changes	02/23/04	M. C.
C	Added 03-NL-BK Material Code.	08/27/07	M. C.
D	Updated Model.	07/23/08	M. C.

PART NO.	H	F	T
460-060	.060 (1.5)	.010 (.25)	.040 (1.0)
460-070	.070 (1.8)	.015 (.38)	
460-080	.080 (2.0)	.020 (.51)	
460-090	.090 (2.3)	.025 (.64)	
460-100	.100 (2.5)	.030 (.76)	
460-110	.110 (2.8)	.035 (.89)	
460-120	.120 (3.0)	.040 (1.0)	
460-130	.130 (3.3)	.045 (1.1)	
460-140	.140 (3.6)	.050 (1.3)	
460-150	.150 (3.8)	.055 (1.4)	
460-160	.160 (4.1)	.060 (1.5)	
460-170	.170 (4.3)	.065 (1.7)	
460-180	.180 (4.6)	.070 (1.8)	
460-190	.190 (4.8)	.075 (1.9)	
460-200	.200 (5.1)	.080 (2.0)	
460-210	.210 (5.3)	.085 (2.2)	

PART NO.	H	F	T
461-360	.360 (9.1)	.010 (.25)	.340 (8.6)
461-380	.380 (9.7)	.020 (.51)	
461-400	.400 (10.2)	.030 (.76)	
461-420	.420 (10.7)	.040 (1.0)	
461-440	.440 (11.2)	.050 (1.3)	
461-460	.460 (11.7)	.060 (1.5)	
461-480	.480 (12.2)	.070 (1.8)	
461-500	.500 (12.7)	.080 (2.0)	
461-520	.520 (13.2)	.090 (2.3)	.540 (13.7)
461-540	.540 (13.7)	.100 (2.5)	

PART NO.	H	F	T
462-560	.560 (14.2)	.010 (.25)	.540 (13.7)
462-580	.580 (14.7)	.020 (.51)	
462-600	.600 (15.2)	.030 (.76)	
462-620	.620 (15.7)	.040 (1.0)	
462-640	.640 (16.3)	.050 (1.3)	
642-660	.660 (16.8)	.060 (1.5)	
462-680	.680 (17.3)	.070 (1.8)	
462-700	.700 (17.8)	.080 (2.0)	
462-720	.720 (18.3)	.090 (2.3)	
462-730	.730 (18.5)	.095 (2.4)	
462-740	.740 (18.8)	.100 (2.5)	

PART NO.	H	F	T
465-200	.200 (5.1)	.025 (.64)	.150 (3.8)
465-210	.210 (5.3)	.030 (.76)	
465-220	.220 (5.6)	.035 (.89)	
465-230	.230 (5.8)	.040 (1.0)	
465-240	.240 (6.1)	.045 (1.1)	
465-250	.250 (6.4)	.050 (1.3)	
465-260	.260 (6.6)	.055 (1.4)	
465-270	.270 (6.9)	.060 (1.5)	
465-280	.280 (7.1)	.065 (1.7)	
465-290	.290 (7.4)	.070 (1.8)	
465-300	.300 (7.6)	.075 (1.9)	
465-310	.310 (7.9)	.080 (2.0)	
465-320	.320 (8.1)	.085 (2.2)	
465-330	.330 (8.4)	.090 (2.3)	
465-340	.340 (8.6)	.095 (2.4)	
465-350	.350 (8.9)	.100 (2.5)	



Note: For 460-XXX, parts are available in black.

3. MATERIAL: NYLON 6/6, 94V-2, BLACK. BIVAR MATERIAL CODE 03-NL-BK.
BASF ULTRAMID NYLON 6/6 A3K, PRE-COLORED IN BLACK.

2. MATERIAL: NYLON 6/6, 94V-2, NATURAL. BIVAR MATERIAL CODE 03-NL.
BASF ULTRAMID NYLON 6/6 A3K NATURAL.

1. GENERAL SPECIFICATIONS: BIVAR MOLDED COMPONENT SPECIFICATION BV00-E101.

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°		TITLE: T-1(3mm) & T-1½(5mm) INDIVIDUAL LED MOUNTS
.XX ± .01			
.XXX ± .005		DESIGNED: David Green	DATE: 08/07/03
		CHECKED: M. Chen	DATE: 08/07/03
		PART NO: 46X-XXX CAGE CODE : 32559 SHEET # 1 OF 1 CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

<u>460-060</u>	<u>460-100</u>	<u>460-110</u>	<u>460-120</u>	<u>460-150</u>	<u>460-200</u>	<u>461-380</u>	<u>465-250</u>	<u>465-350</u>	<u>460-070</u>	<u>460-080</u>	<u>460-090</u>
<u>460-130</u>	<u>460-140</u>	<u>460-160</u>	<u>460-170</u>	<u>460-180</u>	<u>460-190</u>	<u>460-210</u>	<u>461-360</u>	<u>461-400</u>	<u>461-420</u>	<u>461-440</u>	<u>461-460</u>
<u>461-480</u>	<u>461-500</u>	<u>461-520</u>	<u>461-540</u>	<u>462-560</u>	<u>462-580</u>	<u>462-600</u>	<u>462-620</u>	<u>462-640</u>	<u>462-660</u>	<u>462-680</u>	<u>462-700</u>
<u>462-720</u>	<u>462-730</u>	<u>462-740</u>	<u>465-200</u>	<u>465-210</u>	<u>465-220</u>	<u>465-230</u>	<u>465-240</u>	<u>465-260</u>	<u>465-270</u>	<u>465-280</u>	<u>465-290</u>
<u>465-300</u>	<u>465-310</u>	<u>465-320</u>	<u>465-330</u>	<u>465-340</u>							