



REV.	DESCRIPTION	DATE	APPROVED
E	Engineering Update w/o Changes	02/26/04	M. C.
F	Material Update	10/13/08	T.Y.



3. TOLERANCE "L" DIMENSION:

0.030 - 0.500 (1.0 - 12.7mm) ± 0.005 (0.1mm)
0.505 - 0.750 (12.8 - 19.1mm) ± 0.008 (0.2mm)
0.755 - 1.250 (19.2 - 31.8mm) ± 0.015 (0.4mm)

2. MATERIAL: PVC ALLOY, 94V-0, BLACK. BIVAR MATERIAL CODE 58-BK. CYBERSHIELD PVC ALLOY, CS1534WX-BLK02N BLACK.

1. GENERAL SPECIFICATIONS: BIVAR EXTRUDED PRODUCT SPECIFICATION BV00-E105.

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
<u>DECIMALS</u>	<u>ANGULAR</u>		
.X ± .1	X° ± 1°	 TITLE: EXTRUDED, SELF-RETAINING LED MOUNT	
.XX ± .01			
.XXX ± .005		PART NO: ELM 7	
DESIGNED: Shane Irving	DATE: 02/03/98	REVISION: F	
CHECKED: M. Chen	DATE: 12/17/02	CAGE CODE : 32559	SHEET # 1 OF 1
CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[ELM 7-200](#) [ELM 7-025](#) [ELM 7-040](#) [ELM 7-045](#) [ELM 7-050](#) [ELM 7-060](#) [ELM 7-065](#) [ELM 7-070](#) [ELM 7-075](#) [ELM 7-080](#) [ELM 7-090](#) [ELM 7-095](#) [ELM 7-105](#) [ELM 7-110](#) [ELM 7-115](#) [ELM 7-120](#) [ELM 7-125](#) [ELM 7-130](#) [ELM 7-135](#) [ELM 7-140](#) [ELM 7-150](#) [ELM 7-155](#) [ELM 7-180](#) [ELM 7-190](#) [ELM 7-210](#) [ELM 7-230](#) [ELM 7-235](#) [ELM 7-245](#) [ELM 7-260](#) [ELM 7-280](#) [ELM 7-300](#) [ELM 7-310](#) [ELM 7-315](#) [ELM 7-320](#) [ELM 7-325](#) [ELM 7-335](#) [ELM 7-345](#) [ELM 7-350](#) [ELM 7-355](#) [ELM 7-360](#) [ELM 7-375](#) [ELM 7-385](#) [ELM 7-400](#) [ELM 7-435](#) [ELM 7-515](#) [ELM 7-520](#) [ELM 7-525](#) [ELM 7-530](#) [ELM 7-535](#) [ELM 7-540](#) [ELM 7-550](#) [ELM 7-560](#) [ELM 7-580](#) [ELM 7-585](#) [ELM 7-590](#) [ELM 7-600](#) [ELM 7-625](#) [ELM 7-650](#) [ELM 7-655](#) [ELM 7-665](#) [ELM 7-735](#) [ELM 7-750](#) [ELM 7-815](#) [ELM 7-835](#) [ELM 7-855](#) [ELM 7-875](#) [ELM 7-900](#)