



REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release	12/03/07	M. C.
B	Updated LEDs Orientation	01/31/08	M. C.
C	Engineering Update w/o Changes	08/05/16	J. C.
D	ECO-1073 Removed BOM	11/10/20	A. V.
E	ECO-1086 Updated LED Parameters and Rating	02/26/21	A. V.



LED Part No.	Chip			Lens Appearance	Absolute Max. Ratings				Electro-Optical Data @ 20mA			Viewing Angle θ½ (Deg)
	Material	Peak Wave Length λp (nm)	Emitted Color		Δλ (nm)	Pd (mW)	If (mA)	Peak If (mA)	Vf (V)		Iv (mcd)	
									TYP	MAX	TYP	
1.8BC	GaAsP/GaP	640	HE RED	WHITE DIFFUSED	45	100	30	150	2.1	2.6	4.0	70
	GaP/GaP	568	GREEN		30	100	30	150	2.2	2.6	4.0	

CUSTOMER USE DRAWING

ABSOLUTE MAXIMUM RATINGS (Ta = 25°C)

REVERSE VOLTAGE _____ 5V
 REVERSE CURRENT (VR=5V) _____ 100μA
 OPERATING TEMPERATURE RANGE _____ -40°C ~ 80°C
 STORAGE TEMPERATURE _____ -40°C ~ 85°C
 LEAD SOLDERING TEMPERATURE (1/16" FROM BODY) _____ 260°C for 5 Seconds

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°	 TITLE: 1.8mm QUAD-LEVEL 90° LED ASSY, REVERSE POLARITY	
.XX ± .02			
.XXX ± .010		DRAWING NO: H485CBC-RP	
DESIGNED: T. Yin	DATE: 12/03/07	REVISION: E	
REVISED: K. Baron	DATE: 02/26/21	SHEET SIZE: A	CAGE CODE: 32559
CHECKED: A. Valdez	DATE: 02/26/21	SCALE: N/A	SHEET # 1 OF 1

CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

H485CBC-RP