


REV.	DESCRIPTION	DATE	APPROVED
F	Engineering Update w/o Changes	02/26/04	M. C.
G	Material Code Update.	01/06/06	M. C.




3. TOLERANCE "L" DIMENSION:

0.030 - 0.500 (1.0 - 12.7mm)±0.005(0.1mm)
0.505 - 0.750 (12.8 - 19.1mm)±0.008(0.2mm)
0.755 - 1.250 (19.2 - 31.8mm)±0.015(0.4mm)

2. MATERIAL: PVC ALLOY, (94V-0), BLACK. BIVAR MATERIAL CODE 58-BK
CYBERTECH CYBERSHIELD PVC ALLOY CS1534WX-BLK02N BLACK

1. GENERAL SPECIFICATIONS: BIVAR EXTRUDED PRODUCT SPECIFICATION BV00-E105.

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ±.1	X° ± 1°	 TITLE: EXTRUDED, SELF-RETAINING LED HOLDER	
.XX ±.01			
.XXX ±.005			
DESIGNED: Shane Irving	DATE: 02/03/98	PART NO: ERM 1	REVISION: G
CHECKED: M. Chen	DATE: 12/17/02	CAGE CODE : 32559	SHEET # 1 OF 1
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[ERM 1-030](#) [ERM 1-035](#) [ERM 1-040](#) [ERM 1-045](#) [ERM 1-050](#) [ERM 1-055](#) [ERM 1-060](#) [ERM 1-065](#) [ERM 1-070](#)
[ERM 1-075](#) [ERM 1-080](#) [ERM 1-085](#) [ERM 1-095](#) [ERM 1-1.000](#) [ERM 1-1.005](#) [ERM 1-1.010](#) [ERM 1-1.015](#) [ERM 1-1.020](#) [ERM 1-1.025](#) [ERM 1-1.030](#) [ERM 1-1.035](#) [ERM 1-1.040](#) [ERM 1-1.045](#) [ERM 1-1.050](#) [ERM 1-1.055](#) [ERM 1-1.060](#) [ERM 1-1.065](#) [ERM 1-1.070](#) [ERM 1-1.075](#) [ERM 1-1.080](#) [ERM 1-1.085](#) [ERM 1-1.090](#) [ERM 1-1.095](#) [ERM 1-1.100](#) [ERM 1-1.105](#) [ERM 1-1.110](#) [ERM 1-1.115](#) [ERM 1-1.120](#) [ERM 1-1.125](#) [ERM 1-1.130](#) [ERM 1-1.135](#) [ERM 1-1.140](#) [ERM 1-1.145](#) [ERM 1-1.150](#) [ERM 1-1.155](#) [ERM 1-1.160](#) [ERM 1-1.165](#) [ERM 1-1.170](#) [ERM 1-1.175](#) [ERM 1-1.180](#) [ERM 1-1.185](#) [ERM 1-1.190](#) [ERM 1-1.195](#) [ERM 1-1.200](#) [ERM 1-1.205](#) [ERM 1-1.210](#) [ERM 1-1.215](#) [ERM 1-1.220](#) [ERM 1-1.225](#) [ERM 1-1.230](#) [ERM 1-1.235](#) [ERM 1-1.240](#) [ERM 1-1.245](#) [ERM 1-1.250](#) [ERM 1-100](#) [ERM 1-105](#)
[ERM 1-10MM](#) [ERM 1-110](#) [ERM 1-115](#) [ERM 1-11MM](#) [ERM 1-120](#) [ERM 1-125](#) [ERM 1-12MM](#) [ERM 1-130](#) [ERM 1-135](#) [ERM 1-13MM](#) [ERM 1-140](#) [ERM 1-145](#) [ERM 1-14MM](#) [ERM 1-150](#) [ERM 1-155](#) [ERM 1-15MM](#) [ERM 1-160](#) [ERM 1-165](#) [ERM 1-16MM](#) [ERM 1-170](#) [ERM 1-175](#) [ERM 1-17MM](#) [ERM 1-180](#) [ERM 1-185](#) [ERM 1-18MM](#) [ERM 1-190](#) [ERM 1-195](#) [ERM 1-19MM](#) [ERM 1-1MM](#) [ERM 1-200](#) [ERM 1-205](#) [ERM 1-20MM](#) [ERM 1-210](#) [ERM 1-215](#)