




ITEM	Q'TY	PART NUMBER	PART DESCRIPTION
1	1	FLPV-XX	Flexible Light Pipe Adapter,90°, w/LED, See page 2 & 3.
2	1	FLPR1-XX.X	Flexible Light-Pipe Lens Cap Assembly, Rectangular

REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release.	02/01/11	T. Y.
B	Replaced 3UWC-0.6K-F with 3UWC1.035C-F	04/26/12	T. Y.
C	Updated Table For Length "L"	11/15/12	T. Y.

NOTE: FLPV-XX ADAPTER SHIPPED NON-ASSEMBLED



SHORT LEAD CATHODE	LED PART NO.	LONG LEAD CATHODE
RED	3xBCC-F	GREEN
YELLOW	3xBCC-Y/G-F	GREEN
RED	3xBCC-R/Y-F	YELLOW
AMBER	3xBCC-A/G-F	GREEN

ABSOLUTE MAXIMUM RATINGS (Ta=25°C)

REVERSE VOLTAGE	5V
REVERSE CURRENT	100uA
OPERATING TEMPERATURE RANGE	-25° C - 85° C
STORAGE TEMPERATURE	-30° C - 100° C
LEAD SOLDERING TEMPERATURE(1/16" FROM BODY)	260° C FOR 5 SECONDS


STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		BIVAR® 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°		
.XX ± .02			
.XXX ± .010			
DESIGNED: Melanie Myers	DATE: 02/01/11	TITLE: FLEXIBLE LIGHT-PIPE ASSY VERTICAL, RECTANGULAR LENS CAP W/LED	
CHECKED: Raffy Paje	DATE: 02/01/11	PART NO: FLPR1VX.X-XX	REVISION: C
		CAGE CODE : 32559	SHEET # 1 OF 3
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.			

REV.	DESCRIPTION	DATE	APPROVED
	SEE SHEET#1.		

FLPR1VX.X-XX PART NO.	LED Part No.	Chip			Lens Appearance	Absolute Max. Ratings				Electro-Optical Data @ 20mA			Viewing Angle 2 θ ½ (Deg)
		Material	Peak Wave Length λp(nm)	Emitted Color		Δλ (nm)	Pd (mW)	If (mA)	Peak If(mA)	Vf (V)		Iv (mcd)	
										TYP	MAX	TYP	
FLPR1VX.X-SG	3SGC-F	GaP/GaP	568	SUPER GREEN	WATER CLEAR	30	80	30	150	2.2	2.6	120	30
FLPR1VX.X-SY	3SYC-F	GaAsP/GaP	585	SUPER YELLOW	WATER CLEAR	35	80	30	150	2.1	2.6	65	30
FLPR1VX.X-SA	3SAC-F	AlGaInP	620	SUPER AMBER	WATER CLEAR	17	100	30	150	2.0	2.6	350	30
FLPR1VX.X-SR	3SRC-F	GaAiAsP/GaAs	660	SUPER RED	WATER CLEAR	20	80	20	150	1.7	2.6	250	30

FLPR1VX.X-XX PART NO.	LED Part No.	Chip			Lens Appearance	Absolute Max. Ratings				Electro-Optical Data @ 20mA			Viewing Angle 2 θ ½ (Deg)
		Material	Peak Wave Length λp(nm)	Emitted Color		Δλ (nm)	Pd (mW)	If (mA)	Peak If(mA)	Vf (V)		Iv (mcd)	
										Typ.	Max.	Typ.	
FLPR1VX.XUBW.6K	3UBWC-0.6K-F	InGaN/SiC	466	BLUE	WATER CLEAR	26	76	50	150	3.5	4.5	600	20
FLPR1VX.X-UT	3UTC-F	InGaN/SiC	502	TURQUOISE	WATER CLEAR	30	70	30	150	3.5	4.5	900	20
FLPR1VX.X-UG	3UGC-F	InGaAlP	563	GREEN	WATER CLEAR	11	100	30	150	2.2	2.6	800	30
FLPR1VX.X-SUG	3SUGC-F	InGaAlP	574	GREEN	WATER CLEAR	22	100	30	150	2.2	3.0	1000	30
FLPR1VX.X-UY	3UYC-F	InGaAlP	588	YELLOW	WATER CLEAR	15	100	30	150	2.0	2.6	600	20
FLPR1VX.X-SUY	3SUYC-F	InGaAlP	592	YELLOW	WATER CLEAR	15	100	30	150	2.0	2.6	1000	30
FLPR1VX.X-UUY	3UUYC-F	InGaAlP	592	YELLOW	WATER CLEAR	15	100	30	150	2.1	2.6	2000	30
FLPR1VX.X-UO	3UOC-F	AlGaInP	620	ORANGE	WATER CLEAR	17	100	30	150	2.2	2.6	1500	30
FLPR1VX.X-SUO	3SUOC-F	InGaAlP	633	ORANGE	WATER CLEAR	17	100	30	150	2.2	2.6	2200	30
FLPR1VX.X-UR	3URC-F	GaAlAs/GaAs	660	RED	WATER CLEAR	20	60	30	150	1.7	2.6	400	30
FLPR1VX.X-SUR	3SURC-F	GaAlAs/GaAs	660	RED	WATER CLEAR	20	65	30	150	2.0	2.6	600	30
FLPR1VX.XUW0.6K	3UWC1.035C-F	InGaN/SiC	X=.30 Y=.31	WHITE	WATER CLEAR	-	120	20	100	3.4	3.8	1000	35

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED) $\pm 10\%$ ALL VALUES ANGULAR		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DESIGNED: Melanie Myers	DATE: 02/01/11		TITLE: FLEXIBLE LIGHT-PIPE ASSY VERTICAL, RECTANGULAR LENS CAP W/LED
			PART NO: FLPR1VX.X-XX REVISION: C
CHECKED: Raffy Paje	DATE: 02/01/11	CAGE CODE : 32559 SHEET # 2 OF 3 CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.	

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED) ±10% ALL VALUES ANGULAR		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
			
DESIGNED: Melanie Myers		DATE: 02/01/11	
CHECKED: Raffy Paje		DATE: 02/01/11	
		TITLE: FLEXIBLE LIGHT-PIPE ASSY VERTICAL, RECTANGULAR LENS CAP W/LED	
		PART NO: FLPR1VX.X-XX	
		REVISION: C	
		CAGE CODE # 32559 SHEET # 3 OF 3	
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[FLPR1V4.0-SBC](#) [FV1-4.0-UG-F7P-5](#) [FV1-6.0-UR-F7P-2](#) [FV1-12.0-SY-F7P-5](#) [FV1-6.0-SA-F7P-4](#) [FV1-6.0-UT-F7P-6](#)
[FV1-6.0-SBC-Y/G-F7P-2](#) [FV1-12.0-SG-F7P-6](#) [FV1-4.0-UY-F7P-6](#) [FV1-6.0-UY-F7P-4](#) [FV1-4.0-UR-F7P-2](#) [FV1-6.0-](#)
[UG-F7P-5](#) [FV1-6.0-SBC-F7P-5](#) [FV1-12.0-SG-F7P-2](#) [FV1-6.0-SA-F7P-5](#) [FV1-12.0-UR-F7P-9](#) [FV1-6.0-UBW.6K-F7P-4](#)
[FV1-10.0-SG-F7P-5](#) [FV1-3.0-UBW.6K-F7P-4](#) [FV1-6.0-SUO-F7P-9](#) [FV1-12.0-SR-F7P-4](#) [FV1-4.0-UG-F7P-2](#) [FV1-](#)
[12.0-UBW.6K-F7P-2](#) [FV1-6.0-UY-F7P-5](#) [FV1-4.0-UY-F7P-9](#) [FV1-6.0-SBC-F7P-2](#) [FV1-12.0-UR-F7P-2](#) [FV1-6.0-UT-](#)
[F7P-4](#) [FV1-3.0-UBW.6K-F7P-5](#) [FV1-6.0-UG-F7P-2](#) [FV1-12.0-SG-F7P-9](#) [FV1-6.0-UY-F7P-9](#) [FV1-6.0-UT-F7P-5](#) [FV1-](#)
[12.0-UR-F7P-4](#) [FV1-6.0-UBW.6K-F7P-9](#) [FV1-6.0-SBC-F7P-6](#) [FV1-6.0-SUO-F7P-4](#) [FV1-6.0-UBW.6K-F7P-2](#) [FV1-](#)
[10.0-SR-F7P-4](#) [FV1-12.0-SY-F7P-2](#) [FV1-12.0-UR-F7P-5](#) [FV1-4.0-UG-F7P-4](#) [FV1-12.0-UBW.6K-F7P-5](#) [FV1-12.0-SR-](#)
[F7P-9](#) [FV1-10.0-SR-F7P-5](#) [FV1-12.0-SY-F7P-9](#) [FV1-6.0-SBC-Y/G-F7P-4](#) [FV1-6.0-UG-F7P-6](#) [FV1-6.0-UG-F7P-4](#)
[FV1-6.0-UR-F7P-6](#) [FV1-4.0-UG-F7P-9](#) [FV1-4.0-UR-F7P-6](#) [FV1-4.0-UG-F7P-6](#) [FV1-12.0-UBW.6K-F7P-6](#) [FV1-6.0-](#)
[SBC-Y/G-F7P-5](#) [FV1-12.0-UBW.6K-F7P-9](#) [FV1-4.0-UY-F7P-5](#) [FV1-6.0-UR-F7P-9](#) [FV1-4.0-UR-F7P-4](#) [FV1-10.0-SG-](#)
[F7P-6](#) [FV1-6.0-UY-F7P-2](#) [FV1-6.0-UY-F7P-6](#) [FV1-4.0-UR-F7P-5](#) [FV1-12.0-SR-F7P-2](#) [FV1-10.0-SG-F7P-4](#) [FV1-](#)
[10.0-SG-F7P-9](#) [FV1-3.0-UBW.6K-F7P-6](#) [FV1-6.0-SBC-F7P-9](#) [FV1-6.0-UBW.6K-F7P-6](#) [FV1-12.0-SR-F7P-6](#) [FV1-](#)
[12.0-SY-F7P-4](#) [FV1-6.0-UG-F7P-9](#) [FV1-6.0-UR-F7P-4](#) [FV1-6.0-SA-F7P-9](#) [FV1-6.0-SUO-F7P-6](#) [FV1-12.0-SG-F7P-4](#)
[FV1-10.0-SR-F7P-9](#) [FV1-12.0-SY-F7P-6](#) [FV1-10.0-SR-F7P-2](#) [FV1-6.0-SA-F7P-6](#) [FV1-6.0-SA-F7P-2](#) [FV1-12.0-SG-](#)
[F7P-5](#) [FV1-10.0-SG-F7P-2](#) [FV1-10.0-SR-F7P-6](#) [FV1-12.0-SR-F7P-5](#) [FV1-12.0-UBW.6K-F7P-4](#) [FV1-12.0-UR-F7P-6](#)
[FV1-3.0-UBW.6K-F7P-2](#) [FV1-3.0-UBW.6K-F7P-9](#) [FV1-4.0-UR-F7P-9](#) [FV1-4.0-UY-F7P-2](#) [FV1-4.0-UY-F7P-4](#) [FV1-6.0-](#)
[SBC-F7P-4](#) [FV1-6.0-SBC-Y/G-F7P-6](#) [FV1-6.0-SBC-Y/G-F7P-9](#) [FV1-6.0-SUO-F7P-2](#) [FV1-6.0-SUO-F7P-5](#) [FV1-6.0-](#)
[UBW.6K-F7P-5](#) [FV1-6.0-UR-F7P-5](#) [FV1-6.0-UT-F7P-2](#)