



Product: [7917A](#) 



Composite Data, Audio, Video, Security and Control

Product Description

Siamese Composite, Cat 5 4 PR 24 AWG unshielded plus Series 6 Coax with Duobond® II Shield. Polyolefin Insulation on the pairs; Gas-injected FHDPE Insulation on the coax, Overall F-R PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	HDTV, DBS, CATV, CCTV, Multimedia, Voice, Video, Data, High Speed Internet, Networked Computing, Distributed Video, Distributed Audio, Security Monitoring, Energy Monitoring
------------------------	---

Physical Characteristics (Overall)

Conductor						
Element	AWG	Stranding	Material	Nominal Diameter	No. of Pairs	No. of Coax
18 AWG Coax	18	Solid	BC - Bare Copper	0.04 in		1
24 AWG Pairs	24	Solid	BC - Bare Copper	0.02 in	4	
Conductor Count:		9				

Insulation		
Material	Nominal Diameter	Nominal Wall Thickness
PE - Polyethylene (Foam)	0.178 in	0.070 in
PP - Polypropylene	0.035 in	0.0073 in
Table Notes:		Gas Injected

Color Chart	
Number	Color
1	White/Blue Stripe and Blue
2	White/Orange Stripe and Orange
3	White/Green Stripe and Green
4	White/Brown Stripe and Brown

Inner Shield Material				
Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Aluminum		57%
Table Notes:		Tape bonded to dielectric		

Outer Shield Material	
Material	
No Shield	

Outer Jacket Material			
Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.504 in	0.0305 in	Yes

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Inner Shield DCR
93.8 Ohm/km	6.4 Ohm/1000ft	6.4 Ohm/1000ft	9 Ohm/1000ft

Capacitance

Max. Mutual Capacitance	Nom. Capacitance Conductor to Shield	Nom.Mutual Capacitance
17 pF/ft	16.2 pF/ft	15 pF/ft

Inductance

Nominal Inductance
0.097 µH/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

Return Loss (RL)

Frequency [MHz]	Min. Structural Return Loss (SRL)
5-2250 MHz	15 dB

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss	Nom. Structural Return Loss (SRL)
5 MHz	0.5 dB/100ft	15 dB
55 MHz	1.4 dB/100ft	
211 MHz	2.6 dB/100ft	
500 MHz	4.1 dB/100ft	
750 MHz	5.1 dB/100ft	
852 MHz	5.5 dB/100ft	
1000 MHz	6 dB/100ft	
1450 MHz	7.9 dB/100ft	
1800 MHz	8.4 dB/100ft	
2250 MHz	10.1 dB/100ft	

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.2 ns/ft	83%
	70%

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Max./Min. Fitted Impedance
5 MHz	0.67 dB/100ft	62 dB	100 +/- 15%
55 MHz	1.6 dB/100ft	53 dB	100 +/- 15%
211 MHz	2.87 dB/100ft	48 dB	100 +/- 15%
500 MHz	4.48 dB/100ft	47 dB	100 +/- 15%
750 MHz	5.59 dB/100ft	44 dB	100 +/- 15%
862 MHz	5.98 dB/100ft	42 dB	100 +/- 15%
1000 MHz	6.54 dB/100ft	41 dB	100 +/- 15%
1450 MHz	8.3 dB/100ft	39 dB	100 +/- 15%
1800 MHz	9.3 dB/100ft	35 dB	100 +/- 15%
2250 MHz	10.6 dB/100ft	32 dB	100 +/- 15%

Voltage

UL Voltage Rating
300 V RMS

Electrical Characteristics Notes:	5-2250 MHz
-----------------------------------	------------

Temperature Range

Operating Temp Range:	-20°C To +75°C
-----------------------	----------------

Mechanical Characteristics

Bulk Cable Weight:	45.2 lbs/1000ft
Max. Pull Tension:	92 lbs

Min Bend Radius/Minor Axis:	2.75 in
-----------------------------	---------

Standards

NEC/(UL) Compliance:	CM
CEC/C(UL) Compliance:	CM
IEC Compliance:	ISO/IEC 11801, Category 5
TIA/EIA Compliance:	ANSI/TIA/EIA-568-B.2, Category 5
Series Type:	6
Other Compliance:	NEMA WC-63.1, Category 5
Other Compliance:	ISO/IEC 11801, Category 5; ANSI/TIA/EIA-568-B.2, Category 5

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-03-18
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1581 Vertical Tray
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
7917A 3371000	Green, Light	Reel	1,000 ft	612825001430

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	Overall jacket sequentially marked.
--------	-------------------------------------

History

Update and Revision:	Revision Number: 0.201 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[7917A 3371000](#)