



REPRESENTATIVE IMAGE

Product: [7931A](#)

DataTuff® Cat 6, 4 Bonded-Pr #23 Sol BC, FEP Ins, FEP Jkt, CMP CMP-LC

Request Sample

Product Description

Industrial Ethernet Cat 6, 4 Bonded-Pair 23AWG (Solid) Bare Copper, FEP Insulation, FEP Outer Jacket, CMP CMP-LC

Technical Specifications

Product Overview

Suitable Applications:	extreme temp, exposure to oil and gasoline, harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc.
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/resources/patents .

Construction Details

Conductor

AWG	Stranding	Material	Number of Pairs
23	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
FEP - Fluorinated Ethylene Propylene	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown
Bonded-Pair:	Yes

Outer Jacket Material

Material	Nom. Diameter	Ripcord
FEP - Fluorinated Ethylene Propylene	0.214 in	No

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. DCR Unbalance	Max. Capacitance Unbalance	Nom. Mutual Capacitance	Nom. Velocity of Prop.
9.38 Ohm/1000ft	5%	330 pF/ft	15 pF/ft	72%

Delay

Max. Delay	Max. Delay Skew	Nom. Velocity of Propagation (VP) [%]
537 ns/100m	45 ns/100m	72%

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2 dB/100m	74.3 dB	72.3 dB	72.3 dB	70.3 dB	67.8 dB	64.8 dB	20 dB	100 ± 15 Ohm	100 ± 15 Ohm
4 MHz	3.8 dB/100m	65.3 dB	63.3 dB	61.5 dB	59.5 dB	55.8 dB	52.7 dB	23 dB	100 ± 15 Ohm	100 ± 15
8 MHz	5.3 dB/100m	60.8 dB	58.8 dB	55.4 dB	53.4 dB	49.7 dB	46.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 15
10 MHz	6 dB/100m	59.3 dB	57.3 dB	53.3 dB	51.3 dB	47.8 dB	44.8 dB	25 dB	100 ± 15 Ohm	100 ± 15
16 MHz	7.6 dB/100m	56.2 dB	54.3 dB	48.7 dB	46.7 dB	43.7 dB	40.7 dB	25 dB	100 ± 15 Ohm	100 ± 15
20 MHz	8.5 dB/100m	54.8 dB	52.8 dB	46.3 dB	44.3 dB	41.8 dB	38.7 dB	25 dB	100 ± 15 Ohm	100 ± 15
25 MHz	9.5 dB/100m	53.3 dB	51.3 dB	43.8 dB	41.8 dB	39.8 dB	36.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 15
31.25 MHz	10.7 dB/100m	51.9 dB	49.9 dB	41.2 dB	39.2 dB	37.9 dB	34.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 15
62.5 MHz	15.4 dB/100m	47.4 dB	45.4 dB	32 dB	30 dB	31.9 dB	28.8 dB	21.5 dB	100 ± 15 Ohm	100 ± 15

100 MHz	19.8 dB/100m	44.3 dB	42.3 dB	24.5 dB	22.5 dB	27.8 dB	24.8 dB	20.1 dB	100 ± 15 Ohm
155 MHz	25.2 dB/100m	41.5 dB	39.5 dB	16.3 dB	14.3 dB	23.9 dB	20.9 dB	18.8 dB	100 ± 22 Ohm
200 MHz	29 dB/100m	39.8 dB	37.8 dB	10.8 dB	8.8 dB	21.8 dB	18.7 dB	18 dB	100 ± 22 Ohm
250 MHz	32.8 dB/100m	38.3 dB	36.3 dB	5.5 dB	3.5 dB	19.8 dB	16.8 dB	17.3 dB	100 ± 32 Ohm

Voltage

UL Voltage Rating
300 V (CMP)

Mechanical Characteristics

Temperature

UL Rating	Operating	Installation
150°C	-70°C To +150°C	-55°C To +150°C

Bend Radius

Stationary Min.
0.5 in

Max. Pull Tension:	40 lbs
Bulk Cable Weight:	28 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor, Sunlight Resistance, Oil Resistance
Flammability / Fire Resistance:	NFPA 262 Plenum Flame Test (UL910), UL723 (NFPA 255), FT6, FT6, IEC 60332-1-2
NEC / UL Compliance:	800, CMP;FHC 25/50
CEC / C(UL) Compliance:	CMP
Data Category:	Category 6
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6
CPR Euroclass:	Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
7931A 0101000	Black	Reel	1,000 ft	612825191599

Product Notes

Notes:	Operating temperatures subject to length de-rating.
--------	---

History

Update and Revision:	Revision Number: 0.365 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[7931A 0101000](#)