



Part Number: 7933A

DataTuff® Cat 5e, (2 pr) 24 AWG Solid BC, PO/PVC, Foil Shld, EtherNet/IP, CMR

[🛒 Request Sample](#)

Product Description

Two Cat 5e 24 AWG Bonded-Pairs solid bare copper conductors, polyolefin insulation, overall Beldfoil® shield (100% coverage), industrial grade oil- and UV-resistant PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	Industrial Ethernet Cable, Harsh Environments, Category 5e, ProfiNet, 100BaseTX, CMX - Outdoor, PLTC Listed, Approved for Cable Tray Use in Class 1, Division 2, Hazardous Areas and Non-hazardous Areas, Cable Trays, Raceways, Conduit and Supported by Messenger Wires, Approved for Outdoor Usage
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	2

Conductor Count:	4
Total Number of Pairs:	4
Conductor Size:	24 AWG

Insulation

Material	
PO - Polyolefin	
Bonded-Pair:	Yes

Color Chart

Number	Color
1	White/Orange Stripe & Orange
2	White/Green Stripe & Green

Inner Jacket Material

Material	Nominal Diameter
FRPE - Flame Retardant Polyethylene	0.164 mm

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	24	7x32 mm
	TC - Tinned Copper					

Outer Jacket Material

Material	Nominal Diameter
Industrial Grade TPE - Thermoplastic Elastomer	0.265 in

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
5.7 Ohm/1000ft	3 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
150 pF/ft	15 pF/ft

Delay

Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
552 ns/100m	45 ns/100m	70 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. SRL (Structural Return Loss)	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2.1 dB/100m	65.3 dB	62.3 dB	63.2 dB	60 dB	63.8 dB	60.8 dB	23 dB	23 dB	100 ± 20.2 Ohm	105 ±10 Ohm
4 MHz	4.0 dB/100m	56.3 dB	53.3 dB	56.3 dB	49 dB	51.7 dB	48.7 dB	23 dB	23 dB	100 ± 14.2 Ohm	100 ±10 Ohm
8 MHz	5.6 dB/100m	51.8 dB	48.8 dB	46.2 dB	43 dB	45.7 dB	42.7 dB	23 dB	24.5 dB	100 ± 11.3 Ohm	100 ±10 Ohm
10 MHz	6.3 dB/100m	50.3 dB	47.3 dB	43.9 dB	41 dB	43.8 dB	40.8 dB	25 dB	25 dB	100 ± 11.3 Ohm	100 ±10 Ohm
16 MHz	8.0 dB/100m	47.3 dB	44.3 dB	35.2 dB	36 dB	39.7 dB	36.7 dB	25 dB	25 dB	100 ± 11.3 Ohm	100 ±10 Ohm
20 MHz	9.0 dB/100m	45.8 dB	42.8 dB	36.5 dB	33.5 dB	37.7 dB	34.7 dB	25 dB	25 dB	100 ± 11.3 Ohm	100 ±10 Ohm
25 MHz	10.1 dB/100m	44.3 dB	41.3 dB	34.2 dB	30.9 dB	35.8 dB	32.8 dB	25.5 dB	24.3 dB	100 ± 11.3 Ohm	100 ±10 Ohm
31.25 MHz	11.4 dB/100m	42.9 dB	39.9 dB	31.3 dB	28 dB	33.9 dB	30.9 dB	23.6 dB	23.6 dB	100 ± 13.2 Ohm	100 ±10 Ohm
62.5 MHz	16.5 dB/100m	38.4 dB	35.4 dB	21.6 dB	19 dB	27.8 dB	24.8 dB	21.5 dB	21.5 dB	100 ± 16.9 Ohm	100 ±10 Ohm
100 MHz	21.3 dB/100m	35.3 dB	32.3 dB	17.1 dB	11 dB	23.8 dB	20.8 dB	20.1 dB	20.1 dB	100 ± 20.0 Ohm	100 ±10 Ohm
155 MHz	28.1 dB/100m	32.5 dB	29.5 dB	4.4 dB	1.4 dB	19.9 dB	16.9 dB	15.8 dB		100 ± 25 Ohm	100 ± 15 Ohm
200 MHz	32 dB/100m	30.8 dB	27.8 dB	4 dB	1 dB	17.7 dB	14.7 dB	15 dB		100 ± 25 Ohm	100 ± 15 Ohm
1 MHz											
4 MHz											
8 MHz											
10 MHz											
16 MHz											
20 MHz											
25 MHz											
31.25 MHz											
62.5 MHz											
100 MHz											
155 MHz											
200 MHz											

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Installation Temp Range:	-25°C To +60°C
UL Temp Rating:	60°C
Storage Temp Range:	-40°C To +80°C
Operating Temp Range:	-40°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	40.7 lbs/1000ft
Max Recommended Pulling Tension:	55 lbs
Min Bend Radius/Minor Axis:	2.560 in

Standards

NEC/(UL) Specification:	CMG, CMX-Outdoor, ITC, PLTC
CEC/C(UL) Specification:	CMG
ISO/IEC Compliance:	ISO/IEC 11801 ed 2.1 (2008) Class D
CPR Euroclass:	Eca
Data Category:	Category 5e
Telecommunications Standards:	NEMA WC-63.1 Category 5e
Other Specification:	Oil Res II, Oil Res 60811-2-1, Weldsplatter Resistant

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 Vertical Tray Flame Test
CSA Flammability:	FT4
IEEE Flammability:	1202
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Footnote
7933A 0101000	Black	C
7933A 1NH1000	Teal	C

Footnote:	C - CRATE REEL PUT-UP.
Patent:	https://www.belden.com/resources/patents

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.