



Product: [7940A](#)

DataTuff® Cat 6, 4 Bonded-Pr #23 Sol BC, PO Ins, PVC Jkt, CMX-Outdoor CMR

Request Sample

Product Description

Industrial Ethernet Cat 6, 4 Bonded-Pair 23AWG (Solid) Bare Copper, PO Insulation, PVC Outer Jacket, CMX-Outdoor CMR

Technical Specifications

Product Overview

Suitable Applications:	outdoor, harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc.
Patent:	This product has one or more applicable patents. More information on patents can be found at <a href="https://www.belden.com/patents">https://www.belden.com/patents</a> .

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
23 AWG	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
PO - Polyolefin	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Bonded-Pair:	Yes
--------------	-----

Outer Jacket

Separator	Material	Nom. Diameter	Ripcord
Dielectric Tape (Patented)	PVC - Polyvinyl Chloride	0.25 in (6.4 mm)	Yes

Overall Cable Diameter (Nominal):	0.25 in (6.4 mm)
-----------------------------------	------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
82 Ohm/km	330 pF/ft

Delay

Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
537 ns/100m	45 ns/100m	72%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1	2.0 dB/100m	74.3	72.3	72.3	70.3	67.8	64.8	21	100 ± 15 Ohm	100 ± 15 Ohm
4	3.8 dB/100m	65.3	63.3	61.5	59.5	55.8	52.7	24	100 ± 15 Ohm	100 ± 15 Ohm
8	5.3 dB/100m	60.8	58.8	55.4	53.4	49.7	46.7	25.5	100 ± 15 Ohm	100 ± 15 Ohm
10	6 dB/100m	59.3	57.3	53.3	51.3	47.8	44.8	26	100 ± 15 Ohm	100 ± 15 Ohm
16	7.6 dB/100m	56.2	54.3	48.7	46.7	43.7	40.7	26	100 ± 15 Ohm	100 ± 15 Ohm
20	8.5 dB/100m	54.8	52.8	46.3	44.3	41.8	38.8	26	100 ± 15 Ohm	100 ± 15 Ohm
25	9.5 dB/100m	53.3	51.3	43.8	41.8	39.8	36.8	25.3	100 ± 15 Ohm	100 ± 15 Ohm
31.25	10.7 dB/100m	51.9	49.9	41.2	39.2	37.9	34.9	24.6	100 ± 15 Ohm	100 ± 15 Ohm
62.5	15.4 dB/100m	47.4	45.4	32	30	31.9	28.9	22.5	100 ± 15 Ohm	100 ± 15 Ohm

100	19.8 dB/100m	44.3	42.3	24.5	22.5	27.8	24.8	21.1	100 ± 15 Ohm	
155	25.2 dB/100m	41.5	39.5	16.3	14.3	23.9	20.9	19.8	100 ± 22 Ohm	100 ± 15 Ohm
200	29.0 dB/100m	39.8	37.8	10.8	8.8	21.8	18.8	19	100 ± 22 Ohm	100 ± 15 Ohm
250	32.8 dB/100m	38.3	36.3	5.5	3.5	19.8	16.8	18.3	100 ± 32 Ohm	100 ± 15 Ohm

Voltage

UL Voltage Rating
300 V (CMR), 300 V (CMX-Outdoor)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
90°C	-40°C To +75°C	-20°C To +75°C	-40°C To +75°C

Bend Radius

Stationary Min.
2.5 in (64 mm)

Max. Pull Tension:	40 lbs (18 kg)
Bulk Cable Weight:	30 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, Oil Resistance, Aerial
Flammability / Reaction to Fire:	UL1666 Riser, FT4, IEEE 1202 Vertical Tray Flame Test, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMR, CMX-Outdoor
CEC / C(UL) Compliance:	CMX-Outdoor
Data Category:	Category 6
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6
Third Party Performance Verification:	Category 6
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Jacket sequentially marked at 2 ft. intervals.
--------	--

History

Update and Revision:	Revision Number: 0.541 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
7940A 0101000	Black	Reel	1,000 ft	612825191827	C
7940A 0102000	Black	Reel	2,000 ft	612825191834	C
7940A 0061000	Blue	Reel	1,000 ft	612825191803	
7940A 0081000	Gray	Reel	1,000 ft	612825191810	
7940A 1NH1000	Teal	Reel	1,000 ft	612825191841	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[7940A 0101000](#) [7940A 0102000](#) [7940A 0081000](#) [7940A 1NH1000](#) [7940A 0061000](#)