

NOTES:

1. COMPONENTS SHIPPED NON-ASSEMBLED.








TABLE 1 - LENGTH	
LENGTH (L)*	TOLERANCE
1.00" - 16.00"	±0.05"
16.1" - 40.00"	±0.15"
40.1" - 80.00"	±0.30"
80.1" - 3,940.00"	±0.5%

*AVAILABLE IN 0.1" INCREMENTS



REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release	9/14/2009	T.Y.
B	Updated Table For Length "L"	11/14/2012	T.Y.
C	ECO-1241: Updated Recommended Mounting Holes	5/9/2024	A.V.



CUSTOMER USE DRAWING

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°	 TITLE: FLP ASSEMBLY WITH SMFLP ADAPTER, FLAT FACE	
.XX ± .02			
.XXX ± .010		DRAWING NO: SMFLP2F-X.X	REVISION: C
DESIGNED: K. BARON	DATE: 9/14/2009	SHEET SIZE A	CAGE CODE: 32559
REVISED: K. BARON	DATE: 5/9/2024	SCALE: 2:1	SHEET # 1 OF 1
CHECKED: A. VALDEZ	DATE: 5/9/2024	CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[BIVAR:](#)

[SMFLP2F-12.0](#) [SMFLP2F-1.5](#) [SMFLP2F-10.0](#) [SMFLP2F-2.0](#) [SMFLP2F-2.5](#) [SMFLP2F-6.0](#) [SMFLP2F-7.0](#)
[SMFLP2F-9.0](#) [SMFLP2F-9.9](#) [SMFLP2F-1.75](#) [SMFLP2F-24.0](#) [SMFLP2F-2.8](#) [SF4-1.5-R4FP-2](#) [SF4-1.5-R4FP-4](#) [SF4-1.5-R4FP-5](#) [SF4-1.5-R4FP-6](#) [SF4-1.5-R4FP-9](#) [SF4-1.75-R4FP-2](#) [SF4-1.75-R4FP-4](#) [SF4-1.75-R4FP-5](#) [SF4-1.75-R4FP-6](#) [SF4-1.75-R4FP-9](#) [SF4-10.0-R4FP-2](#) [SF4-10.0-R4FP-4](#) [SF4-10.0-R4FP-5](#) [SF4-10.0-R4FP-6](#) [SF4-10.0-R4FP-9](#) [SF4-12.0-R4FP-2](#) [SF4-12.0-R4FP-4](#) [SF4-12.0-R4FP-5](#) [SF4-12.0-R4FP-6](#) [SF4-12.0-R4FP-9](#) [SF4-2.5-R4FP-2](#) [SF4-2.5-R4FP-4](#) [SF4-2.5-R4FP-5](#) [SF4-2.5-R4FP-6](#) [SF4-2.5-R4FP-9](#) [SF4-2.8-R4FP-2](#) [SF4-2.8-R4FP-4](#) [SF4-2.8-R4FP-5](#) [SF4-2.8-R4FP-6](#) [SF4-2.8-R4FP-9](#) [SF4-24.0-R4FP-2](#) [SF4-24.0-R4FP-4](#) [SF4-24.0-R4FP-5](#) [SF4-24.0-R4FP-6](#) [SF4-24.0-R4FP-9](#) [SF4-6.0-R4FP-2](#) [SF4-6.0-R4FP-4](#) [SF4-6.0-R4FP-5](#) [SF4-6.0-R4FP-6](#) [SF4-6.0-R4FP-9](#) [SF4-7.0-R4FP-2](#) [SF4-7.0-R4FP-4](#) [SF4-7.0-R4FP-5](#) [SF4-7.0-R4FP-6](#) [SF4-7.0-R4FP-9](#) [SF4-9.9-R4FP-2](#) [SF4-9.9-R4FP-4](#) [SF4-9.9-R4FP-5](#) [SF4-9.9-R4FP-6](#) [SF4-9.9-R4FP-9](#)