



**Product:** [8079](#)

Magnet Wire, #26 Sol BC, Polyester/Amide-imide Polymer Ins

Request Sample

### Product Description

Magnet Wire, 26AWG (Solid) Bare Copper, Polyester/Amide-imide Polymer Insulation, CLASS 200 MW 35-C

### Technical Specifications

#### Product Overview

|                        |                       |
|------------------------|-----------------------|
| Suitable Applications: | class 200 magnet wire |
|------------------------|-----------------------|

#### Physical Characteristics (Overall)

##### Conductor

| AWG | Stranding | Material         | No. of Conductors |
|-----|-----------|------------------|-------------------|
| 26  | Solid     | BC - Bare Copper | 1                 |

|                  |   |
|------------------|---|
| Conductor Count: | 1 |
|------------------|---|

##### Insulation

| Material  | Nominal Diameter | Nominal Wall Thickness |
|-----------|------------------|------------------------|
| Polyester | 0.0182 in        | 0.002 in               |

##### Outer Jacket

| Max. Diameter |
|---------------|
| 0.0182 mm     |

#### Construction and Dimensions

|                     |          |
|---------------------|----------|
| Min Increase in OD: | 0.002 in |
|---------------------|----------|

#### Electrical Characteristics

##### Conductor DCR

| Nominal Conductor DCR |
|-----------------------|
| 41 Ohm/1000ft         |

##### Current

| Max. Recommended Current [A]                |
|---|
| Single conductor in free air @ 30°C: 0.36 A |

##### Voltage

| Breakdown Voltage                    |
|--------------------------------------|
| 4600 V Minimum (at Room Temperature) |

#### Temperature Range

|                     |       |
|---------------------|-------|
| Non-UL Temp Rating: | 200°C |
|---------------------|-------|

#### Mechanical Characteristics

|                        |         |
|------------------------|---------|
| Approximate Length:    | 1260 ft |
| Turns Per Linear Inch: | 55.7    |

|                              |                |
|------------------------------|----------------|
| Turns Per Square Inch:       | 3102           |
| Bulk Cable Weight:           | 0.8 lbs/1000ft |
| Min. Bend Radius/Minor Axis: | 0.08 in        |

## Standards

|                      |             |
|----------------------|-------------|
| Military Compliance: | J-W-1177/14 |
|----------------------|-------------|

## Applicable Environmental and Other Programs

|  |                               |
|--|-------------------------------|
| EU Directive 2000/53/EC (ELV):               | Yes                           |
| EU Directive 2003/96/EC (BFR):               | Yes                           |
| EU Directive 2011/65/EU (RoHS 2):            | Yes                           |
| EU Directive 2012/19/EU (WEEE):              | Yes                           |
| EU Directive 2015/863/EU (RoHS 2 amendment): | Yes                           |
| EU Directive Compliance:                     | EU Directive 2003/11/EC (BFR) |
| EU CE Mark:                                  | Yes                           |
| CA Prop 65:                                  | Yes                           |
| MII Order #39 (China RoHS):                  | Yes                           |

## Flammability, LSOH, Toxicity Testing

|                    |     |
|--------------------|-----|
| UL voltage rating: | N/A |
|--------------------|-----|

## Plenum/Non-Plenum

|               |    |
|---------------|----|
| Plenum (Y/N): | No |
|---------------|----|

## Related Part Numbers

### Variants

| Item # | Color | Put-Up Type | Length | UPC          |
|--------|-------|-------------|--------|--------------|
| 8079   | None  | Reel        | 1 ft   | 612825194613 |

## History

|                      |  |
|----------------------|--|
| Update and Revision: | Revision Number: 0.380 Revision Date: 05-05-2023 |
|----------------------|--|

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[8079](#)