


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	02/18/16	D.N.



#10-32 UNF

.250 HEX

#10-32 UNF

"D" FLAT

Ø.035

Ø.062

NOTES:

MATERIALS:


1. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
2. LOCKWASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.
3. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

1. CONTACTS = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.
2. ALL OTHER METAL PARTS = GOLD PLATE PER ASTM B488-11, TYPE II, 30µin MIN, GRADE C OVER 100 TO 200µin COPPER STRIKE PER AMS 2418.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON	
DECIMAL	ANGLE

DWN:	DATE
D.N.	02/18/16
CHKD:	DATE
N.D.	02/18/16
APVD:	DATE
J.M.	02/18/16



Property of Radiall

This document cannot be reproduced or
communicated to a third party without prior
written permission of RADIALL.

**SMC RIGHT ANGLE MALE JACK
BULKHEAD FRONT MOUNT
SOLDER POT RECEPTACLE**

REFERENCE:	MATERIALS & FINISHES:	SIZE	FSCM NO.	DWG NO.	REV
ORIGINATED: D.N. DATE: 02/18/16	SEE NOTES	A	19505	1012-1511-000	A
		SCALE 5:1		THIRD ANGLE PROJECTION	SHEET 1 OF 1

1012-1511-000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[1012-1511-000](#)