



Product: [82512](#)

RS-232, #24-12.5pr, FEP, O/A Foil, LS-PVC Jkt, CMP

Product Description

Computer EIA RS-232 Cable, 12.5-Pair, 24 AWG stranded (7x32) tinned copper conductors, FEP insulation, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, Flamarrest® jacket, plenum rated.

Technical Specifications

Product Overview

Suitable Applications:	indoor plenum applications; RS-232 applications; computer communications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; panel wiring
------------------------	---

Construction Details

Conductor				
Element	No. of Elements	Size	Stranding	Material
Pair(s)	12	24 AWG	7x32	TC - Tinned Copper
Conductor(s)	1	24 AWG	7x32	TC - Tinned Copper

Insulation				
Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	FEP - Fluorinated Ethylene Propylene	0.006 in (0.15 mm)	0.036 in (0.91 mm)	Black & Red, Black & White, Black & Green, Black & Blue, Black & Yellow, Black & Brown, Black & Orange, Red & White, Red & Green, Red & Blue, Red & Yellow, Red & Brown, Yellow
Conductor(s)	FEP - Fluorinated Ethylene Propylene	0.006 in (0.15 mm)	0.036 in (0.91 mm)	Yellow

Outer Shield			
Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Outer Jacket		
Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.278 in (7.06 mm)
Overall Cable Diameter (Nominal): 0.278 in (7.06 mm)		

Electrical Characteristics

Electricals				
Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Pair(s)	24.1 Ohm/1000ft	23 pF/ft (75 pF/m)	42 pF/ft (140 pF/m)	1.5 Amps per Conductor at 25°C

Voltage	
UL Voltage Rating	300 V (CMP)

Mechanical Characteristics

Temperature	
UL Temperature	Operating
60°C	0°C to +60°C

Bend Radius

Stationary Min.	Installation Min.
2.8 in (71 mm)	2.8 in (71 mm)

Max. Pull Tension:	143 lbs (64.9 kg)
Bulk Cable Weight:	56 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), FT6
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.538 Revision Date: 12-22-2023
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
82512 8771000	Natural	612825197270	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[82512 8771000](#)