


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/28/11	D.N.





NOTES:

MATERIALS:

1. BODY & CONTACT = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.
2. INSULATOR = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
3. SLEEVE = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

1. BODY & SLEEVE = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 0, GRADE C, OVER .00010 TO .00020 COPPER STRIKE PER MIL-C-14550.
2. CONTACT = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 1, GRADE C, OVER .00010 TO .00020 STRESS FREE SULFAMATE NICKEL PER QQ-N-290.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN:	DATE	 Property of Radiall This document cannot be reproduced or communicated to a third party without prior a RADIAL company written permission of RADIAL.	
		D.N.	11/28/11		
DECIMAL	ANGLE	CHKD:	DATE	SSLB STRAIGHT FEMALE PLUG P.C.B. MOUNT RECEPTACLE	
		J.S.	11/28/11		
		APVD:	DATE	SIZE A	FSCM NO. 19505
		J.M.	11/28/11		
REFERENCE:		MATERIALS & FINISHES:		DWG. NO. 7325-1512-000	REV A
ORIGINATED: D.N. DATE: 11/28/11		SEE NOTES			
		SCALE 8:1		THIRD ANGLE PROJECTION	SHEET 1 OF 1

7325-1512-000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[7325-1512-000](#)