


PAGE 1/4	ISSUE 18-02-19A	SERIES OCTIS	PART NUMBER OCTI207550
----------	-----------------	--------------	------------------------



All dimensions are in mm. Tolerances according ISO 2768 m-H

DESCRIPTION

REP	COMPONENT	MATERIALS	PLATING
1	Screwable Receptacle Body	ALUMINIUM	CHEMICAL PASSIVATION
2	Panel Sealing Gasket	SILICONE	-

PAGE 2/4

ISSUE 18-02-19A

SERIES OCTIS


PART NUMBER OCTI207550

GENERAL CHARACTERISTICS

Mechanical Mating endurance (cycles) Vibration Weight (g)	IEC 61300-2-2 IEC 61300-2-1 -	100 - 6,9630
Environmental Protection class Operating temperature (°C) Storage temperature (°C) Salt Mist RoHS Flammability UVB Resist (h)	IEC 60529 IEC 61300-2-22 IEC 61300-2-22 IEC 61300-2-26 (ISO21207 method B) - UL 94 ASTM G154 cycle 2	IP67 * -40 / +85 -65 / +85 720h * Compliant V0 1000
Others: Equipment interface Packaging	- -	For use with OCTIS™ plug or receptacle cap 20 pcs by tray

* Mated condition

PANEL CUT OUT





	mm	
	Min.	Max.
A	19.7	19.9
B	31.9	32.1
C	16.5	16.8
D	M3	-
E	19.5	20
F	-	0.5

PAGE 3/4	ISSUE 18-02-19A	SERIES OCTIS	PART NUMBER OCTI207550
----------	-----------------	--------------	------------------------



PACKAGING:

Packaging in Hot Formed Tray



POSITIONNING AND PATTERN DEFINITION

Tab Down



Contact RADIALL to know which socket brands are compatible with OCTIS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Radial:](#)

[OCTI207550](#)