



Product: [82743](#)

Electronic, 6 Pr #22 Str TC, FEP Ins, PVC Jkt, CMP

[Request Sample](#)

Product Description

High Temperature Electronic, 6 Pair 22AWG (7x30) Tinned Copper, FEP Insulation, PVC Outer Jacket, CMP

Technical Specifications

Product Overview

Suitable Applications:	indoor plenum applications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

Physical Characteristics (Overall)

Conductor			
AWG	Stranding	Material	No. of Pairs
22	7x30	TC - Tinned Copper	6
Conductor Count:			12
Total Number of Pairs:			6

Insulation	
Material	Nominal Wall Thickness
FEP - Fluorinated Ethylene Propylene	0.0065 in

Color Chart	
Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue
5	Black & Yellow
6	Black & Brown

Outer Shield

Material
No Shield

Outer Jacket

Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	Flamarrest®	0.238 in	0.0145 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
16 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
21 pF/ft

Inductance

Nominal Inductance
0.15 µH/ft

Impedance

Nominal Characteristic Impedance
80 Ohm

Current

Max. Recommended Current [A]
3.3 Amps per Conductor at 25°C (10°C Temperature Rise)

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Operating Temperature Range:	0°C To +75°C
------------------------------	--------------

Mechanical Characteristics

Bulk Cable Weight:	42 lbs/1000ft
Max. Pull Tension:	109 lbs
Min. Bend Radius/Minor Axis:	2.5 in

Standards

NEC Articles:	Article 800
NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262
CSA Flammability:	FT6
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Related Part Numbers

Non-Plenum Number:	8743
--------------------	------

Variants

Item #	Color	Put-Up Type	Length	UPC
82743 8771000	Natural	Reel	1,000 ft	612825197690

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.384 Revision Date: 12-22-2023
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[82743 8771000](#)