



**Product:** [8337](#)

RS232, Low Cap, #24-7pr, SR-PVC, O/A Foil+Braid, PVC Jkt, CMG

## Product Description

Computer EIA RS-232 Cable, 7-Pair, 24 AWG stranded (7x32) tinned copper conductors, semi-rigid PVC insulation, overall Beldfoil® (100% coverage) + tinned copper braid shield (65% coverage), PVC jacket.

## Technical Specifications

### Product Overview

Suitable Applications:	RS-232 extended distance applications; computer communications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; panel wiring
------------------------	---

### Construction Details

#### Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	7	24 AWG	7x32	TC - Tinned Copper

#### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	SR-PVC - Polyvinyl Chloride (Semi-Rigid)	0.0105 in (0.267 mm)	0.044 in (1.1 mm)	Western Electric Standard

#### Outer Shield

Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	100%
Braid	Tinned Copper (TC)	65%

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.035 in (0.89 mm)	0.321 in (8.15 mm)

Overall Cable Diameter (Nominal):	0.321 in (8.15 mm)
-----------------------------------	--------------------

### Electrical Characteristics

#### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
Pair(s)	28.8 Ohm/1000ft	30 pF/ft (98 pF/m)	50 pF/ft (160 pF/m)	75 Ohm	60%	1.96 Amps per Conductor at 25°C

#### Voltage

UL Voltage Rating
300 V (CMG), 300 V (UL AWM 2464)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
80°C	-30°C to +80°C

Bend Radius

Stationary Min.	Installation Min.
3.2 in (81 mm)	3.2 in (81 mm)

Max. Pull Tension:	82 lbs (37 kg)
Bulk Cable Weight:	60 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2464, AWM I A
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.463 Revision Date: 12-22-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8337 060100	Chrome	Reel	100 ft	612825204541	
8337 060500	Chrome	Reel	500 ft	612825204565	
8337 0601000	Chrome	Reel	1,000 ft	612825204558	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[8337 060100](#) [8337 0601000](#) [8337 060500](#)