



Product: [83652](#)

Electronic, 2 C #18 Str TC, FEP Ins, OS+TC Brd, FEP Jkt, CMP

[Request Sample](#)

Product Description

High Temperature Electronic, 2 Conductor 18AWG (19x30) Tinned Copper, FEP Insulation, Overall Beldfoil®+Tinned Copper Braid(85%) Shield, FEP Outer Jacket, CMP

Technical Specifications

Product Overview

| | |
|------------------------|---|
| Suitable Applications: | extreme high/low temperature environments; chemical resistant; outdoor and burial applications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring |
|------------------------|---|

Construction Details

Conductor

| Element | No. of Elements | Size | Stranding | Material |
|--------------|-----------------|--------|-----------|--------------------|
| Conductor(s) | 2 | 18 AWG | 19x30 | TC - Tinned Copper |

Insulation

| Element | Material | Nom. Thickness | Nom. Insulation Diameter | Color Code |
|--------------|--------------------------------------|--------------------|--------------------------|--------------|
| Conductor(s) | FEP - Fluorinated Ethylene Propylene | 0.007 in (0.18 mm) | 0.057 in (1.4 mm) | Black, White |

Outer Shield

| Shield Type | Material | Coverage |
|-------------|-------------------------|----------|
| Tape | Bi-Laminate (Alum+Poly) | 100% |
| Braid | Tinned Copper (TC) | 85% |

Outer Jacket

| Material | Nom. Thickness | Nom. Diameter |
|--------------------------------------|--------------------|--------------------|
| FEP - Fluorinated Ethylene Propylene | 0.015 in (0.38 mm) | 0.173 in (4.39 mm) |

| | |
|-----------------------------------|--------------------|
| Overall Cable Diameter (Nominal): | 0.173 in (4.39 mm) |
|-----------------------------------|--------------------|

Electrical Characteristics

| Electricals | | | | |
|-------------------|--------------------|-------------------------------|---|------------------------------|
| Element | Nom. Conductor DCR | Nom. Capacitance Cond-to-Cond | Nom. Capacitance Cond-to-Other (Conds + Shield) | Max. Current |
| Conductor(s) | 7.06 Ohm/1000ft | 33 pF/ft (110 pF/m) | 60 pF/ft (200 pF/m) | 5 Amps per Conductor at 25°C |
| Voltage | | | | |
| UL Voltage Rating | | | | |
| 300 V | | | | |

Mechanical Characteristics

| Temperature | |
|----------------|-----------------|
| UL Temperature | Operating |
| 150°C | -70°C to +200°C |

Bend Radius

| Stationary Min. | Installation Min. |
|-----------------|-------------------|
| 1.7 in (43 mm) | 1.7 in (43 mm) |

| | |
|--------------------|----------------|
| Max. Pull Tension: | 79 lbs (36 kg) |
| Bulk Cable Weight: | 26 lbs/1000ft |

Standards and Compliance

| | |
|----------------------------------|--|
| Environmental Suitability: | Indoor, Outdoor, Oil Resistance, Burial |
| Sustainability: | CA Prop 65 |
| Flammability / Reaction to Fire: | NFPA 262 (UL 910), FT6, IEC 60332-1-2 |
| CPR Compliance: | CPR Euroclass: Eca |
| NEC / UL Compliance: | Article 800, CMP |
| CEC / C(UL) Compliance: | CMP |
| European Directive Compliance: | EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE) |
| UK Regulation Compliance: | UKCA Mark |
| APAC Compliance: | China RoHS II (GB/T 26572-2011) |

Product Notes

| | |
|--------|---------------|
| Notes: | Gas Resistant |
|--------|---------------|

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.518 Revision Date: 02-15-2024 |
|----------------------|--|

Part Numbers

Variants

| Item # | Color | Putup Type | Length | UPC | Footnote |
|---------------|-------|------------|----------|--------------|----------|
| 83652 002100 | Red | Reel | 100 ft | 612825205227 | C |
| 83652 002500 | Red | Reel | 500 ft | 612825205258 | C |
| 83652 0021000 | Red | Reel | 1,000 ft | 612825205234 | C |
| 83652 0022000 | Red | Reel | 2,000 ft | 612825205241 | |
| 83652 0025000 | Red | Reel | 5,000 ft | 612825205265 | |

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[83652 002500](#) [83652 002100](#) [83652 0021000](#) [83652 0025000](#)