




JACK RECEPTACLE FRONT MOUNTING
WITH SOLDER POT CONTACT
R161.532.020

Series : N



All dimensions are in mm.

COMPONENTS	MATERIALS	PLATING
BODY	BRASS	BBR 2 µm
CENTRE CONTACT	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL 2 µm
OUTER CONTACT	-	- µm
INSULATOR	PTFE	-
GASKET	-	- µm
OTHERS PARTS	-	-
-	-	-
-	-	-

JACK RECEPTACLE FRONT MOUNTING**WITH SOLDER POT CONTACT****R161.532.020**

Series : N

ELECTRICAL CHARACTERISTICS

Impedance	50 Ω
Frequency	0-11 GHz
VSWR	1.3 + 0.000 x F(GHz) Maxi
Insertion loss	0.048 √F(GHz) dB
RF leakage	- (- F(GHz)) dB mini
Voltage rating	1400 Veff Maxi
Dielectric withstanding voltage	2500 Veff mini
Insulation resistance	5000 MΩ mini

SPECIFICATION

Stripping	a	b	c	d	e	f
mm	0.00	0.00	0.00	0.00	0.00	0.00

Assembly instruction : **A**

Recommended cable(s)

MECHANICAL CHARACTERISTICS

Centre contact retention	
Axial force – Mating end	27 N mini
Axial force – Opposite end	27 N mini
Torque	NA N.cm mini

Cable retention

- pull off	NA N mini
- torque	- N.cm

TOOLING

Part Number	Description	Hexagon
.	.	.

Recommended torque

Mating	NA N.cm
Panel nut	NA N.cm
Clamp nut	NA N.cm
A/F clamp nut	0.000 mm

OTHERS CHARACTERISTICS

Mating life	500 Cycles mini
Weight	17.500 g

ENVIRONMENTAL

Operating temperature	-55/+165 °C
Leakage – pressurised only	NA Atm.cm3/s
Hermetic seal	NA Mpa

**RADIALL®**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

R161532020