



Part Number: 8643

Audio/Control/Instrumentation, (3) 30 AWG (7x38) TC, PP/PVC, TC Braid Shld

[Request Sample](#)

Product Description

Three 30 AWG stranded (7x38) tinned copper conductors, conductors cabled around textile strength member, polypropylene insulation, tinned copper braid shield (95% shield coverage), PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Conductors
30	7x38	TC - Tinned Copper	0.012 in	3
Conductor Count:				3
Conductor Size:				30 AWG

Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	0.006 in

Color Chart

Number	Color
1	Black
2	Red
3	White

Outer Shield Material

Type	Material	Coverage [%]
Braid	TC - Tinned Copper	95 %

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Separator Material
PVC - Polyvinyl Chloride	0.096 in	0.014 in	Paper Tape

Construction and Dimensions

Cabling

Filler
Textile Strength Member

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
98.5 Ohm/1000ft	11.1 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
25 pF/ft	43 pF/ft

Current

Max. Recommended Current [A]

0.9 Amps per conductor @ 25°C

Voltage

Non-UL Voltage Rating

200 V RMS

Temperature Range

Non-UL Temp Rating:	105°C
Operating Temp Range:	-20°C To +105°C

Mechanical Characteristics

Bulk Cable Weight:	8 lbs/1000ft
Max Recommended Pulling Tension:	22.5 lbs
Min Bend Radius/Minor Axis:	1 in

Standards

CPR Euroclass:	Eca
----------------	-----

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-10-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color
8643 060100	Chrome
8643 060250	Chrome

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.