




**STRAIGHT PRESS-MOUNT SCHROUD**
**SMOOTH BORE**
**R222.402.721**


Series : SMP



PANEL CUT OUT



| mm |      |      |
|----|------|------|
|    | Maxi | mini |
| A  | 4.39 | 4.37 |



All dimensions are in mm.

| COMPONENTS     | MATERIALS       | PLATINGS (μm) |
|----------------|-----------------|---------------|
| BODY           | STAINLESS STEEL | PASSIVATED .  |
| CENTER CONTACT |                 |               |
| OUTER CONTACT  |                 |               |
| INSULATOR      |                 |               |
| GASKET         |                 |               |
| OTHERS PARTS   |                 |               |
| -              | -               | -             |
| -              | -               | -             |

Issue : 0529 B

In the effort to improve our products, we reserve the right to make changes judged to be necessary.



**STRAIGHT PRESS-MOUNT SCHROUD****R222.402.721****SMOOTH BORE**

Series : SMP

**PACKAGING**

| Standard   | Unit              | Other             |
|------------|-------------------|-------------------|
| <b>100</b> | <b>'W' option</b> | <b>Contact us</b> |

**SPECIFICATION****ELECTRICAL CHARACTERISTICS**

|                                 |      |                          |
|---------------------------------|------|--------------------------|
| Impedance                       | NA   | $\Omega$                 |
| Frequency                       | NA   | GHz                      |
| VSWR                            | NA + | 0.000 x F(GHz) Maxi      |
| Insertion loss                  | NA   | $\sqrt{F}$ (GHz) dB Maxi |
| RF leakage                      | - (  | NA - F(GHz)) dB Maxi     |
| Voltage rating                  | NA   | Veff Maxi                |
| Dielectric withstanding voltage | NA   | Veff mini                |
| Insulation resistance           | NA   | M $\Omega$ mini          |

**ENVIRONMENTAL**

|                       |         |              |
|-----------------------|---------|--------------|
| Operating temperature | -65/165 | $^{\circ}$ C |
| Hermetic seal         | NA      | Atm.cm3/s    |
| Panel leakage         | NA      |              |

**OTHERS CHARACTERISTICS**

Assembly instruction

Others :

**MECHANICAL CHARACTERISTICS**

|                            |       |             |
|----------------------------|-------|-------------|
| Center contact retention   |       |             |
| Axial force – Mating end   | NA    | N mini      |
| Axial force – Opposite end | NA    | N mini      |
| Torque                     | NA    | N.cm mini   |
| Recommended torque         |       |             |
| Mating                     | NA    | N.cm        |
| Panel nut                  | NA    | N.cm        |
| Mating life                | 1000  | Cycles mini |
| Weight                     | 0.158 | g           |

Issue : 0529 B

In the effort to improve our products, we reserve the right to make changes judged to be necessary.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[R222402721](#) [R222402721W](#)