



Product: [8663](#)

Shielding & Bonding, TC Braid #11.9AWG

[Request Sample](#)

Product Description
Shielding & Bonding, TC Braid 11.9AWG (168x34)

Technical Specifications

Product Overview

Suitable Applications:	for shielding and bonding cable
------------------------	---------------------------------

Construction Details

Conductor				
Element	No. of Elements	Size	Stranding	Material
Braid	1	11.9	168x34	TC - Tinned Copper

Electrical Characteristics

Electricals	
Nom. Conductor DCR	Max. Current
1.55 Ohm/1000ft	Single conductor in free air @ 30°C: 38.0 A

Mechanical Characteristics

Temperature	
UL Temperature	Operating
80°C	-40°C To +80°C
Max. Pull Tension:	64 lbs (29 kg)
Bulk Cable Weight:	24 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Outdoor
Sustainability:	CA Prop 65
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

Product Notes

Notes:	AWG size is approximated.
--------	---------------------------

History

Update and Revision:	Revision Number: 0.453 Revision Date: 07-03-2024
----------------------	--

Part Numbers

Variants				
Item #	Color	Putup Type	Length	UPC
8663 00050	None	Reel	50 ft	612825213949
8663 000250	None	Reel	250 ft	612825213932

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[8663 00050](#) [8663 000250](#)