




STRAIGHT PLUG SOLDER TYPE

R222.900.200

CABLE .085

Series : SMP-COM



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
BODY	BRASS	NPGR
CENTER CONTACT	BERYLLIUM COPPER	NPGR
OUTER CONTACT	BERYLLIUM COPPER	NPGR
INSULATOR	PTFE	
GASKET	-	
OTHERS PARTS	BRASS	NPGR
-	-	-
-	-	-

Issue : 0846 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary.



STRAIGHT PLUG SOLDER TYPE

CABLE .085

R222.900.200

Series : SMP-COM

PACKAGING

Standard	Unit	Other
100	'W' option	Contact us

ELECTRICAL CHARACTERISTICS

Impedance	50	Ω
Frequency	0-12.4*	GHz
VSWR	1.15** + 0,0000	x F(GHz) Maxi
Insertion loss	0.12	$\sqrt{F}$ (GHz) dB Maxi
RF leakage	- (55***	- F(GHz)) dB Maxi
Voltage rating	335	Veff Maxi
Dielectric withstanding voltage	500	Veff mini
Insulation resistance	5000	M Ω mini

MECHANICAL CHARACTERISTICS

Center contact retention	
Axial force – Mating end	NA N mini
Axial force – Opposite end	NA N mini
Torque	NA N.cm mini

Recommended torque	
Mating	N.cm
Panel nut	N.cm
Clamp nut	N.cm
A/F clamp nut	0,0000 mm

Mating life	100 Cycles mini
Weight	0,6500 g

ENVIRONMENTAL

Operating temperature	-55/+105 °C
Hermetic seal	NA Atm.cm3/s
Panel leakage	NA

SPECIFICATIONCABLE ASSEMBLY

Stripping	a	b	c	d	e	f
mm	1,30	0,00	0,00	0,00	0,00	0,00

Assembly instruction :

Recommended cable(s)

KS 1

RG 405

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the assembly

Cable retention

- pull off	200 N mini
- torque	NA N.cm

TOOLING

Part Number	Description	Hexagon
.	.	.
R282.051.000	STRIPPING TOOL	
R282.062.010	POINTER GAUGE	
R282.740.030	SOLDERING MOUNTING	
R282.743.120	POSITIONER FOR SOLDERING SMP	
R282.744.253	POSITIONER FOR SOLDERING SMP	
R282.862.050	SOLDER GAUGE THCK .012	

OTHER CHARACTERISTICS

*ROS: 1.35 at 12.4GHz

**ROS at 6GHz

***RF Leakage : -40dB min 3<F<6GHz



Issue : 0846 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

**RADIALL**®

STRAIGHT PLUG SOLDER TYPE**R222.900.200****CABLE .085**


Series : SMP-COM

COMPONENTS**STRIPPING CABLES**


We recommend a thermal preconditionning cable

1


Strip the dielectric of the cable .
Trim the cable .
Clean the cable .
Iron temperature not exceed 250°C

**2**

Screw the positoner onto the soldering jig.
Slide center contact into positoner.
Insert solder gauge between contact and cable .
Tighten and solder the contact.

**3**

After cooling remove cable assembly from the jig.
Slide body into positoner .
Slide cable into the connector until it bottoms against the positoner .
Tighten.
Solder the body onto the cable.
After cooling remove cable assembly from the jig.



Issue : 0846 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

**RADIALL**

®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[R222900200W](#)