


STRAIGHT MALE RECEPTACLE PIN IN PASTE


R222.940.300

LIMITED DETENT-TAPE AND REEL BY 500

Series : SMP-COM



All dimensions are in mm.



PLATING (μm)

COMPONENTS	MATERIALS	PLATING (μm)
BODY	BRASS	NPGR
CENTER CONTACT	BRASS	NPGR
OUTER CONTACT	-	-
INSULATOR	PEEK	-
GASKET	-	-
OTHERS PARTS	-	-
-	-	-
-	-	-

Issue : 1121 C

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

STRAIGHT MALE RECEPTACLE PIN IN PASTE
LIMITED DETENT-TAPE AND REEL BY 500

R222.940.300

Series : SMP-COM

PACKAGING

Standard	Unit	Other
500		Contact us

SPECIFICATION

ELECTRICAL CHARACTERISTICS

Impedance	50 Ω
Frequency	0-12.4* GHz
VSWR	1.1** + 0,0000 x F(GHz) Maxi
Insertion loss	0.12 $\sqrt{F(GHz)}$ dB Maxi
RF leakage	- (NA - F(GHz)) dB Maxi
Voltage rating	335 Veff Maxi
Dielectric withstanding voltage	500 Veff mini
Insulation resistance	5000 M Ω mini

ENVIRONMENTAL

Operating temperature	-55/+125 °C
Hermetic seal	NA Atm.cm ³ /s
Panel leakage	NA

OTHER CHARACTERISTICS

Assembly instruction	NA
----------------------	-----------

Others :

* ROS 1.35 at 12.4Ghz

**ROS at 6GHz

MECHANICAL CHARACTERISTICS

Center contact retention	
Axial force – Mating end	6.8 N mini
Axial force – Opposite end	6.8 N mini
Torque	NA N.cm mini

Recommended torque	
Mating	NA N.cm
Panel nut	NA N.cm

Mating life	100 Cycles mini
Weight	0,3610 g

Issue : 1121 C

In the effort to improve our products, we reserve the right to make changes judged to be necessary.




STRAIGHT MALE RECEPTACLE PIN IN PASTE**LIMITED DETENT-TAPE AND REEL BY 500****R222.940.300**

Series : SMP-COM

SOLDER PROCEDURE

1. Deposit solder paste 'SnAg4Cu0.5' on mounting zone by screen printing application. We recommend a low residue flux. We advise a thickness of 150 micromm (5.850 microinch). Verify that the edges of the zone are clean.
2. Placement of the receptacle on the mounting zone with an automatic machine of 'pick and place' type. A video camera is recommended for positioning of the component . Adhesive agents must not be used on the receptacle.
3. This process of soldering has been tested with convection oven .Below please find ,the typical profile to use.
4. The cleaning of printed circuit boards is not obliged .
5. Verification of solder joints and position of the component by visual inspection.

TEMPERATURE PROFILE

Parameter	Value	Unit
Temperature rising Area	1 - 4	°C/sec
Max Peak Temperature	260	°C
Max dwell time @260°C	10	sec
Min dwell time @235°C	20	sec
Max dwell time @235°C	60	sec
Temperature drop in cooling Area	-1 to - 4	°C/sec
Max dwell time above 100°C	420	sec

Issue : 1121 C

In the effort to improve our products, we reserve the right to make changes judged to be necessary.





STRAIGHT MALE RECEPTACLE PIN IN PASTE

R222.940.300

LIMITED DETENT-TAPE AND REEL BY 500

Series : SMP-COM



STANDARD PAD(For ROGERS 4350)SHADOW OF RECEPTACLE FOR VIDEO CAMERA

Issue : 1121 C

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

STRAIGHT MALE RECEPTACLE PIN IN PASTE**LIMITED DETENT-TAPE AND REEL BY 500****R222.940.300**

Series : SMP-COM

AIR SUCTION

Issue : 1121 C

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Radiall](#):

[R222940300](#)