


STRAIGHT CRIMP DIELECTRIC FEEDTROUGHES




P.C.B CABLE 2/50

R280.282.000


Series : ACC-COAX



PANEL CUT OUT



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
BODY	BRASS	NICKEL 2
CENTER CONTACT	-	-
OUTER CONTACT	-	-
INSULATOR	-	-
GASKET	-	-
OTHERS PARTS	BRASS	NICKEL 2
-	-	-
-	-	-

Issue : 0116 E

In the effort to improve our products, we reserve the right to make changes judged to be necessary.


RADIALL

STRAIGHT CRIMP DIELECTRIC FEEDTROUGHES**P.C.B CABLE 2/50****R280.282.000**

Series : ACC-COAX

PACKAGING

Standard	Unit	Other
100	'W' option	Contact us

ELECTRICAL CHARACTERISTICS

Impedance	50	Ω
Frequency	0 - 3	GHz
VSWR	+ 0.000	x F(GHz) Maxi
Insertion loss	.	$\sqrt{F}(\text{GHz})$ dB Maxi
RF leakage	- (	- F(GHz)) dB Maxi
Voltage rating	750	Veff Maxi
Dielectric withstanding voltage	2000	Veff mini
Insulation resistance		M Ω mini

MECHANICAL CHARACTERISTICS

Center contact retention	
Axial force – Mating end	N mini
Axial force – Opposite end	N mini
Torque	N.cm mini

Recommended torque	
Mating	N.cm
Panel nut	N.cm
Clamp nut	N.cm
A/F clamp nut	0.000 mm

Mating life	0 Cycles mini
Weight	0.000 g

ENVIRONMENTAL

Operating temperature	-55/+155 °C
Hermetic seal	Atm.cm3/s
Panel leakage	

SPECIFICATION**4T 201128/00 - -****CABLE ASSEMBLY**

Stripping	a	b	c	d	e	f
mm	4.00	7.00	12.0	0.00	0.00	0.00

Assembly instruction : **Crimp 11**

Recommended cable(s)

KX 21

RG 178 LC

P513064

RG 178 FTX

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the assembly

Cable retention

- pull off	N mini
- torque	N.cm

TOOLING

Part Number	Description	Hexagon
.	.	.
R282.211.000	CRIMPING TOOL	2.67

OTHER CHARACTERISTICS

-

Issue : 0116 E

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

**RADIALL**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

R280282000