

This information is given as an indication. In the continual goal to improve our products, we reserve the right to make any modifications judged necessary

2 W

DC- 8 GHz


SMC

COAXIAL ATTENUATOR

issue
15.jul.93

Page
1 / 1

DRAWING



General tolerances: +/- 0.5 mm

R F CHARACTERISTICS

FREQUENCY RANGE : DC - 8 GHz
IMPEDANCE : 50 Ohms
ATTENUATION - NOMINAL : 10 dB

FREQUENCY	DC- 4 GHz	4 - 8 GHz
V.S.W.R	<= 1.15	<= 1.30
DEVIATION (dB)	+ 0.4 / - 0.4	+ 0.5 / - 0.5

TEMPERATURE SENSITIVITY : $4 \times 10^{-4} \frac{\text{dB}}{\text{dB} \times ^\circ\text{C}}$

PEAK POWER at 25°C (1μs,1%.) : 100 W

AVERAGE POWER at 25°C : 2 W


MECHANICAL CHARACTERISTICS

CONNECTORS : SMC male/female per MIL-C 39012
WEIGHT : < 5 g

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE RANGE (°C) : -55 , +125
STORAGE TEMPERATURE RANGE (°C) : -55 , +125

Power derating
Versus temperature



QUALITY
Dpt app._____
CREATION
PEN : CAT
EP : -----
Nom : KL
Date:13.apr.90

15.jul.93 New issue

ISSUE

REVISIONS

NAME

RADIAL[®]

101. Philibert Hoffmann | Phone:33.1.49353535
- Z.I Ouest - | Fax :33.1.48546363
93116 ROSNY/BOIS Cedex-FRANCE | Twx RADIA 235220F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[R410110121](#)