



**Product:** [8772NH](#)

Electronic, 3C #20 Str TC, PO ins, OS, LSNH Jkt 300V

**Product Description**

Electronic, 3 Conductor AWG 20 Tinned Copper - Stranded, Polyolefin (PO, PE, PP) insulation, Foil(s) or Copper Tape(s) shielding, LSZH / FRNC jacket , 300V

**Technical Specifications**

**Product Overview**

Suitable Applications:	Instrumentation and computer cable; For data transmission applications
------------------------	--

**Physical Characteristics (Overall)**

<b>Conductor</b>			
AWG	Stranding	Material	No. of Conductors
20	7x28	TC - Tinned Copper	3
Conductor Count:			3

<b>Insulation</b>			
Material	Nominal Diameter	Diameter +/- Tolerance	Nominal Wall Thickness
PE - Polyethylene	1.78 mm	0.05 mm	0.017 in

<b>Color Chart</b>	
Number	Color
Wire 1	Black
Wire 2	Red
Wire 3	Clear

<b>Outer Shield</b>							
Type	Material	Material Trade Name	Coverage [%]	Thickness of Foil	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil® (Z-Fold®)	100%	9 / 12 µm	TC - Tinned Copper	AWG20/7	7x28

<b>Outer Jacket</b>		
Material	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	5.65 mm	0.9 mm

**Construction and Dimensions**

<b>Cabling</b>	
Description	Twists
3 wires twisted to cable core	6 twist/ft

**Electrical Characteristics**

<b>Conductor DCR</b>	
Nominal Conductor DCR	Nominal Outer Shield DCR
34.5 Ohm/km	30.8 Ohm/km

**Capacitance**

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
88.6 pF/m	167.3 pF/m

Impedance

Nominal Characteristic Impedance
69 Ohm

Delay

Nominal Velocity of Propagation (VP) [%]
66%

Current

Element	Max. Recommended Current [A]
Conductor(s)	4 A

Voltage

Voltage Rating [V]
300 V

Temperature Range

Installation Temperature Range:	-15°C To +80°C
Storage Temperature Range:	-30°C To +80°C
Operating Temperature Range:	-15°C To +80°C
Operating Temp Range (Fixed Install):	-15°C To +80°C

Mechanical Characteristics

Oil Resistance:	IEC 60811-404
Bulk Cable Weight:	28 lbs/1000ft
Max. Pull Tension:	180 N
Min. Bend Radius During Installation:	56.5 mm
Min. Bend Radius/Minor Axis:	2 in

Standards

CPR Euroclass:	Dca-s1,d1,a1
CENELEC Compliance:	EN 50290-2-20

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Dca
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	Yes

Flammability, LS0H, Toxicity Testing

IEC Flammability:	IEC 60332-1-2, IEC 60332-3-24
IEC 60754-1 - Halogen Amount:	Zero
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 - Smoke Density Min. Transmittance:	60%

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	EAN
8772NH.00500	Blue	Reel	500 m	8719605019448

8772NH.001000	Blue	Reel	1,000 m	8719605019431
8772NH.01152	Chrome	Reel	152 m	8719605019462
8772NH.01500	Chrome	Reel	500 m	8719605019479
8772NH.011000	Chrome	Reel	1,000 m	8719605019455

History

Update and Revision:	Revision Number: 0.307 Revision Date: 06-28-2024
----------------------	--

© 2024 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[8772NH 060500](#) [8772NH 0601000](#)